

[See all 4 Products in Family](#)

0.55 NA, 5.30mm FL, RPO VIS Molded Glass Aspheric Lens



Stock #73-658 **7 In Stock**

- 1 + £108.⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	£108.80 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

7.33 +0/-0.020 **Diameter (mm):**

5.83 **Clear Aperture CA (mm):**

2.93 **Center Thickness CT (mm):**

Protective as needed

Bevel:

Optical Properties

5.30 **Effective Focal Length EFL (mm):**

0.55 **Numerical Aperture NA:**

H-ZLaF52 **Substrate:**

633 **Aspheric Design Wavelength (nm):**

BBAR (400 - 600nm) **Coating:**

$R_{avg} < 1\%$ @ 400 - 600nm **Coating Specification:**

60-40 **Surface Quality:**

0.72 **f#:**

400 - 600 **Wavelength Range (nm):**

3.59 **Working Distance (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses are available with various focal lengths and numerical apertures and are AR coated for >99% transmission from 400 - 600nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.