

TECHSPEC[®] 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens



0.5X Magnification

Stock **#62-913** 20+ In Stock

-

1

+

£2,492⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£2,492.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Series:

PlatinumTL™ Series

Stock No. of Mounting Clamp:

[#63-441](#) Sold Separately

Telecentric Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
184.00	Length (mm):
90.0	Maximum Diameter (mm):
1096	Weight (g):
6.56	Flange Distance (mm):
Optical Properties	
44.8mm	Horizontal Field of View, APS-C Sensor:
57.4mm	Field of View, 28.7mm Sensor:
34.6mm	Horizontal Field of View, 4/3" Sensor:
28.4mm	Horizontal Field of View, 1.1" Sensor:
25.6mm	Horizontal Field of View, 1" Sensor:
17.70mm	Horizontal Field of View, 2/3" Sensor:
12.8mm	Horizontal Field of View, 1/2" Sensor:
28.70	Maximum Image Circle (mm):
0.041	Numerical Aperture NA, Object Side:
10 (7)	Number of Elements (Groups):
<0.055	Typical Telecentricity @ 588nm (°):
<0.020	Typical Distortion @ 588nm (%):
0.5X	Primary Magnification PMAG:
0.50	Telecentric Lens Magnification:
175.00	Working Distance (mm):
44.8 x 33.6	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/22	Aperture (f/#):
425 - 675nm BBAR	Coating:
±2.05 at f/10 (20% @20 lp/mm)	Depth of Field (mm):
0.5X	Magnification:
VS	Lens Wavelength Range:
Sensor	
APS-C	Maximum Sensor Format:
2.74	Pixel Size (µm):
Threading & Mounting	
M86 x 1.00 (Female)	Filter Thread:
M42 x 1.0	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS


- High Resolution f/6 Bi-Telecentric Lens for Measurement
- Up to 35 MegaPixels, 2.8µm Pixel Size Sensors
- APS-C, C-Mount, T-Mount, F-Mount Telecentric Lens
- Magnification from 0.28X to 1.7X

TECHSPEC® PlatinumTL™ Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. The precision designs feature high telecentricity (<0.1°), low distortion (<0.1%), and high light throughput with an adjustable aperture that achieves f/6 when fully open. Capable of supporting large format 28.7mm diagonal sensors, these lenses are compatible with the Sony IMX342 APS-C sensor and other similar format sensors such as the Sony IMX530. TECHSPEC® PlatinumTL™ Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. These lenses are suitable for high vibration environments and feature a removable recessed set screw for securing the iris in place.


TECHNICAL INFORMATION




#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Distortion Plot



#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Relative Illumination Plot




#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Telecentricity Plot



#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 175mm Working Distance, f6



#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Depth of Field Plot, 175mm Working Distance, f6



#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 175mm Working Distance, f10



#62-913, 0.5X, 28.7mm M42 x 1.0 (6.56mm) PlatinumTL™ Telecentric Lens, Depth of Field Plot, 175mm Working Distance, f10

Description		Stock No.	Flange	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mbunt	#62-933	17.5mm	230.8mm	60.5mm	33.5mm

0.5X	C-Mbunt	#62-932	17.5mm	174.9mm	50mm	33.5mm
1.7X	C-Mbunt	#63-232	17.5mm	189.5mm	60mm	46mm
0.28X	F-Mbunt	#62-922	46.5mm	167.6mm	138.6mm	55mm
	M42 x 1.0	#62-923	6.56mm	208.5mm	138.6mm	50mm
	M42 x 1.0	#62-924	19.53mm	195.5mm	138.6mm	50mm
0.5X	F-Mbunt	#62-912	46.5mm	143mm	90mm	55mm
	M42 x 1.0	#62-913	6.56mm	184mm	90mm	50mm
	M42 x 1.0	#62-914	19.53mm	171.1mm	90mm	50mm
0.9X	F-Mbunt	#62-902	46.5mm	170.8mm	65mm	55mm
	M42 x 1.0	#62-903	6.56mm	210.7mm	65mm	53mm
	M42 x 1.0	#62-904	19.53mm	197.8mm	65mm	53mm
