

## TECHSPEC® 0.69X In-Line Illumination CobaltTL Telecentric Lens



Stock #15-873 **5 In Stock**

⊖ 1 ⊕ £2,432<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£2,432.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

CobaltTL Series **Product Family:**

#63-233- Sold Separately **Stock No. of Mounting Clamp:**

Telecentric Lens **Type:**

**Type of Illumination:**

## Physical & Mechanical Properties

Variable	<b>Iris Option:</b>
179.00	<b>Length (mm):</b>
175.00	<b>Length excluding Threads (mm):</b>
55	<b>Maximum Diameter (mm):</b>
792.4	<b>Weight (g):</b>

## Optical Properties

20.39mm	<b>Horizontal Field of View, 1.1" Sensor:</b>
18.55mm	<b>Horizontal Field of View, 1" Sensor:</b>
12.75mm	<b>Horizontal Field of View, 2/3" Sensor:</b>
10.43mm	<b>Horizontal Field of View, 1/1.8" Sensor:</b>
9.27mm	<b>Horizontal Field of View, 1/2" Sensor:</b>
17.60	<b>Maximum Image Circle (mm):</b>
0.058	<b>Numerical Aperture NA, Object Side:</b>
9 (7)	<b>Number of Elements (Groups):</b>
0.69X	<b>Primary Magnification PMAG:</b>
0.69	<b>Telecentric Lens Magnification:</b>
110	<b>Working Distance (mm):</b>
20.4 x 15.3	<b>FOV @ Max Sensor Format, H x V (mm):</b>
f/4.5 - f/22	<b>Aperture (f/#):</b>
λ/4 MgF <sub>2</sub>	<b>Coating:</b>
±1.08mm at f/10 (20% @ 20 lp/mm)	<b>Depth of Field (mm):</b>
0.69X	<b>Magnification:</b>
<0.027	<b>Typical Distortion @ 520nm (%):</b>
<0.086	<b>Typical Telecentricity @ 520nm (°):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1.1"	<b>Maximum Sensor Format:</b>
2.20	<b>Pixel Size (µm):</b>

## Threading & Mounting

M52 x 0.75 (Female)	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>


## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------


- High Resolution Bi-Telecentric Lens with In-Line Illumination Options
- Up to 20 MegaPixels, 2.2 $\mu$ m Pixel Size
- 1.1", C-Mount Telecentric Lens with  $f$ #s as Low as  $f/4$

TECHSPEC® CobaltTL Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. These telecentric lenses achieve high light throughput with industry leading low  $f$ #s. Featuring less than 0.015° telecentricity and low 0.013% distortion, these lenses are ideal for image stitching applications. These 17.6mm diagonal sensor format lenses are compatible with the Sony IMX304 1.1" sensors and other similar format sensors such as the Sony IMX183. TECHSPEC® CobaltTL Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. In-line versions provide the ability to rotate/reposition the inline illumination port to allow for maximum flexibility when machine building. TECHSPEC® CobaltTL Telecentric Lenses are compatible with high vibration environments and feature a removable recessed set screw for securely locking the iris in place.


## Technical Information




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Distortion Plot




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Relative Illumination Plot




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Telecentricity Plot




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance,  $f/6$



#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Depth of Field Plot, 110mm Working Distance,  $f/6$



#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f10



#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f10

#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens					
Description		Stock No.	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-921	197.59mm	138.6mm	50mm
0.36X	C-Mount	#88-602	163.5mm	70mm	43.5mm
0.5X	C-Mount	#62-911	172.9mm	90mm	50mm
0.55X	C-Mount	#88-603	182.5mm	62mm	43.5mm
0.69X	C-Mount	#15-872 / #15-873 (In-Line)	174.96mm	55mm	46mm
0.9X	C-Mount	#62-901	199.8mm	65mm	53mm