

[See all 16 Products in Family](#)

**TECHSPEC® 0.75X In-Line Illumination SilverTL™ Telecentric Lens**



0.75X In-Line Illumination SilverTL™ Telecentric Lens, #88-346



Stock **#88-346** **6 In Stock**

⊖ 1 ⊕ £1,564<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£1,564.00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

SilverTL™ Series **Product Family:**

**Stock No. of Mounting Clamp:**  
#56-870 Sold Separately

Telecentric Lens **Type:**

In-Line Illumination **Type of Illumination:**

## Physical & Mechanical Properties

Variable **Iris Option:**

155.20 **Length (mm):**

155.20 **Length excluding Threads (mm):**

36.00 **Maximum Diameter (mm):**

227 **Weight (g):**

Anodized Aluminum **Construction:**

## Optical Properties

11.7mm **Horizontal Field of View, 2/3" Sensor:**

8.5mm **Horizontal Field of View, 1/2" Sensor:**

6.4mm **Horizontal Field of View, 1/3" Sensor:**

11.00 **Maximum Image Circle (mm):**

0.062 **Numerical Aperture NA, Object Side:**

±3 **Working Distance Tolerance (mm):**

>40% @ 40 lp/mm **Resolution, Image Space MTF @ f/10:**

7 (6) **Number of Elements (Groups):**

<0.080 **Typical Telecentricity @ 588nm (°):**

<0.080 **Typical Distortion @ 588nm (%):**

0.75X **Primary Magnification PMAG:**

0.75 **Telecentric Lens Magnification:**

100.00 **Working Distance (mm):**

11.7 x 8.8 **FOV @ Max Sensor Format, H x V (mm):**

f/6 - f/22 **Aperture (f/#):**

425 - 675nm BBAR **Coating:**

±0.8 at f/10 (20% @ 20 lp/mm) **Depth of Field (mm):**

0.75X **Magnification:**

VIS **Lens Wavelength Range:**

## Sensor

2/3" **Maximum Sensor Format:**

2.74 **Pixel Size (µm):**

## Threading & Mounting

M30.5 x 0.50 (Female) **Filter Thread:**

C-Mount **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**


## Product Details

- High Resolution f/6 Bi-Telecentric Lens with Inline Illumination Options
- Up to 7.5 MegaPixels, 2.8 $\mu$ m Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.16X to 4X


TECHSPEC® SilverTL™ Telecentric Lenses are ideal for both on-line and off-line machine vision production applications that require accurate measurements. These lenses combine high-quality optics with a simplified non-focusing mechanical design and an adjustable iris with a locking set screw. These lenses are designed for metrology and gauging applications. TECHSPEC® SilverTL™ Telecentric Lenses also offer inline illumination options for maximum versatility. Each lens also features a standard front filter thread for use with [color filters](#), [polarizers](#), [protective windows](#), and [illumination adapters](#) for LED or fiber-optic ring lights.

**Note:** Mounting brackets are available that fit the 30mm diameter mounting surface.


## Technical Information




#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Distortion Plot



#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Relative Illumination Plot




#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Telecentricity Plot




#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 100mm Working Distance, f6



#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Depth of Field Plot, 100mm Working Distance, f6





#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 100mm Working Distance, f10



#88-346, 0.75X In-Line Illumination SilverTL™ Telecentric Lens, Depth of Field Plot, 100mm Working Distance, f10

Stock Number	Primary Mag.	Max. Diameter A	Mounting Diameter B	Length C	Mounting Length D	Mounting Offset E	Filter Thread F
#56-675	0.16X	65mm	30mm	191mm	50mm	43mm	M62 x 0.75
#63-073	0.20X	60mm	30mm	188mm	42mm	45mm	M58 x 0.75
#56-676	0.25X	48mm	30mm	158mm	49mm	44mm	M46 x 0.75
#58-428	0.30X	46mm	30mm	158mm	60mm	43mm	M43 x 0.75
#56-677	0.40X	45mm	30mm	159mm	67mm	33mm	M43 x 0.75
#63-074	0.50X	40mm	30mm	153mm	42mm	68mm	M37 x 0.75
#88-344 (In-Line)				156.2mm	45.1mm	73.4mm	
#56-678	0.60X	42mm	30mm	156mm	57mm	46mm	M40.5 x 0.5
#67-731	0.75X	36mm	30mm	151.2mm	34mm*	82.2mm	M30.5 x 0.5
#88-346 (In-Line)				155.2mm	46.2mm	16.9mm	
#58-430	1.0X	40mm	30mm	114mm	32mm*	17mm	M37 x 0.75
#58-431	2.0X	45mm	30mm	141mm	45mm	17mm	M43 x 0.75
#88-348 (In-Line)				144.6mm	42.2mm	18.8mm	
#58-432	4.0X	61mm	30mm	249mm	99mm	17mm	M58 x 0.75



\*Mounting clamp fits over iris

