

[See all 33 Products in Family](#)

## 10 x 10mm, 500µm Pitch, 2.2° Div., Cyl. Microlens Array, UV-VIS



Stock #72-602 [CONTACT US](#)

⊖ 1 ⊕ £765<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	£765.00 each
Qty 11+	£615.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Lens Array **Type:**

### Physical & Mechanical Properties

10.0 x 10.0 ±0.05 **Dimensions (mm):**

3.000 **Radius R (mm):**

1.20 ±0.05 **Thickness (mm):**

## Optical Properties

6.60 **Effective Focal Length EFL (mm):**

**Fused Silica** (Coming 7980) **Substrate:**

UV-NIR (250-700nm) **Coating:**

250 - 700 **Wavelength Range (nm):**

**Coating Specification:**  
R<sub>abs</sub> ≤1.0% from 350 - 450nm @ 0° AOI  
R<sub>avg</sub> ≤1.5% @ 250 - 700nm @ 0°

±2.2 **Divergence Angle (°):**

500.00 ±0.25 **Pitch (µm):**

Single-Sided **Array Type:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 250:**

## Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.