


[See all 32 Products in Family](#)

1064nm, 18-23mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_1064_Q-20

See More by [AdiOptica](#)



Focal Flat Top Beam Shaper



Stock #12-237 **1 In Stock**

⊖ 1 ⊕ £2,528⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£2,528.00 each
Qty 5-10	£2,272.00 each
Qty 11+	£2,150.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
πShaper_1064_Q-20

Beam Shaper **Type:**

[#12-323](#) **Compatible Adapter:**

Physical & Mechanical Properties

21.00 **Length (mm):**

70 **Weight (g):**

38 **Clear Aperture CA (mm):**

64.00 **Diameter (mm):**

18 - 23 **Input Beam Diameter, $1/e^2$ (mm):**

Optical Properties

>99 **Transmission (%):**

1064 **Design Wavelength DWL (nm):**

1020 - 1100 **Wavelength Range (nm):**

TEM₀₀ **Input Beam Mode:**

<1.5 **Typical Input Beam Mode Quality, M^2 :**

±20 **Input Beam Divergence (mrad):**

Electrical

0.4 **Maximum Input Power, CW (kW):**

Threading & Mounting

M58 x 1 **Inner Thread:**

M58 x 1 **Outer Thread:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica \$\pi\$ Shaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal- π Shaper (π Shaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the π Shaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal- π Shapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

