

[See all 5 Products in Family](#)

TECHSPEC®

1064nm, 25mm Diameter, Thin Film Laser Line Beamsplitter



TECHSPEC High Energy Laser Line Polarizers

Stock **#21-893** **3 In Stock**

-

1

+

£432⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£432.00 each
Qty 6-25	£377.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Plate Beamsplitter	Type:
Physical & Mechanical Properties	
90	Clear Aperture (%):
22.50	Clear Aperture CA (mm):

Thin Film Dielectric	Construction:
25.00	Diameter (mm):
+0.00/-0.25	Dimensional Tolerance (mm):
6.00 ±0.25	Thickness (mm):
Optical Properties	
45±2	Angle of Incidence (°):
1064	Design Wavelength DWL (nm):
10,000:1	Extinction Ratio:
>98	P-Polarization Transmission (%):
>99	S-Polarization Reflection (%):
Fused Silica	Substrate: ☐
40-20	Surface Quality:
λ/4 @ 633nm	Transmitted Wavefront, P-V:
2 J/cm² @ 532nm, 10ns, S or P Polarization	Damage Threshold, By Design: ☐
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 45° Angle of Incidence
- Reflects S-Polarized Light, Transmits P-Polarized Light
- Available for Nd:YAG Harmonics and HeNe Wavelengths

TECHSPEC® Laser Line Polarizing Plate Beamsplitters split randomly polarized light into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. These beamsplitters feature thin film dielectric coatings which provide high laser damage thresholds for optimal performance in many laser applications. TECHSPEC® Laser Line Polarizing Plate Beamsplitters UV grade fused silica substrate maximizes performance while the hard anti-reflection coating makes them durable and easy to clean.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).