

[See all 215 Products in Family](#)

TECHSPEC® 10mm Dia., 0.50 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-415** **3 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £199²⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | £199.20 each |
| Qty 6-10 | £179.20 each |
| Qty 11-25 | £163.20 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

10.00 +0.00/-0.025 **Diameter (mm):**

| | |
|----------------------|---------------------------|
| <3 | Centering (arcmin): |
| 9.00 | Clear Aperture CA (mm): |
| 6.18 | Edge Thickness ET (mm): |
| 7.80 ±0.10 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |

| | |
|-------|------------------------|
| Plano | Shape of Back Surface: |
|-------|------------------------|

Optical Properties

| | |
|-----------------|----------------------------------|
| 10.00 @ 587.6nm | Effective Focal Length EFL (mm): |
| 0.50 | Numerical Aperture NA: |

| | |
|-----------------------|-------------------------------------|
| 5.68 | Back Focal Length BFL (mm): |
| N-SF6 | Substrate: <input type="checkbox"/> |

| | |
|-------|--------------------------------------|
| 587.6 | Aspheric Design Wavelength (nm): |
| 0.4λ | Asphere Figure Error, RMS @ 632.8nm: |

| | |
|----------|------------------|
| Uncoated | Coating: |
| 40-20 | Surface Quality: |

| | |
|-------|--------------------------------|
| 1.00 | f#: |
| 25.36 | Abbe Number (v _d): |

| | |
|------------|--|
| 1.805 | Index of Refraction (n _d): |
| 390 - 2500 | Wavelength Range (nm): |

| | |
|----------|---|
| Infinite | Conjugate Distance: |
| 587.6 | Focal Length Specification Wavelength (nm): |

| | |
|--------|-------------------|
| 100.00 | Power (diopters): |
|--------|-------------------|

Material Properties

| | |
|-----|--|
| 9.0 | Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C): |
|-----|--|

Regulatory Compliance

| | |
|---------------------------|-----------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |

| | |
|---------------------------|------------|
| Compliant | Reach 233: |
|---------------------------|------------|

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts