

[See all 8 Products in Family](#)

TECHSPEC®

10mm Dia. 1030nm 45°, Yb:YAG Laser Line Mirror



Yb:YAG ZERODUR Laser Line Mirrors

Stock **#26-894** **9 In Stock**

-

1

+

£151²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£151.20 each
Qty 6-25	£132.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

2.00 +/-0.2

Thickness (mm):

10.00 +0.00/-0.20

Diameter (mm):

90	Clear Aperture (%):
30	Parallelism (arcsec):
Optical Properties	
ZERODUR®	Substrate: ☐
20-10	Surface Quality:
45	Angle of Incidence (°):
Laser Mirror (1030nm)	Coating:
1030	Design Wavelength DWL (nm):
99.8	Reflection at DWL (%):
1020 - 1040	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Coating Specification: R _{abs} > 99.80% @ 1030nm @ 45° AOI R _{avg} > 99.5% @ 1020 - 1040nm @ 45° AOI	
Dielectric	Coating Type:
Damage Threshold, By Design: ☐ 20 J/cm² @ 1030nm, 20ns, 20Hz	
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
 - >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
 - High Laser Damage Threshold Specifications
- Yb:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Yb:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are great for applications where the optics will be exposed to fluctuating temperatures. The Yb:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Yb:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering.