

TECHSPEC[®] 10mm, VIS 0° Coated, Rhomboid Prism



Stock **#47-807** 20+ In Stock

-

1

+

£93⁵⁰ ~~£155.84~~

ADD TO CART

Volume Pricing	
Qty 1-5	£155.84 £93.50 each
Qty 6-25	£124.32 £74.59 each
Qty 26-49	£116.44 £69.86 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Rhomboid Prism


Physical & Mechanical Properties	
10.00	Length (mm):
±0.1	Dimensional Tolerance (mm):
Optical Properties	
±5	Angle Tolerance (arcsec):
±30	Beam Deviation (arcsec):
VS 0° (425-675nm)	Coating:
N-BK7	Substrate: ☐
40-20	Surface Quality:
Beam Deviation	Image Orientation:
R _{avg} ≤0.4% @ 425 - 675nm	Coating Specification:
0	Ray Deviation (°):
425 - 675	Wavelength Range (nm):
Entrance/Exit Surfaces: 5 J/cm² @ 532nm, 10ns	Damage Threshold, Reference: ☐
1.00	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
View	Certificate of Conformance:


PRODUCT DETAILS

- Lateral Displacement of Beam
- Displaces Optical Axis Without Inverting Image
- Input and Output Beams Parallel to ±30 Arcseconds
- Beam Displacing [Dove Prisms](#) Also Available


TECHSPEC® Rhomboid prisms are commonly used to displace a laser beam without changing its direction. In imaging applications, rhomboid prisms will displace the optical axis without inverting the image. The lateral displacement is equal to the length of the prism (specified by dimension D). TECHSPEC® Rhomboid Prisms feature high tolerance angles that keep the output beam parallel to the input beam to within 30 arcseconds. They are ideal for demanding displacement applications.

TECHNICAL INFORMATION






Rhomboid Prism Ray Path



Rhomboid Prism Tunnel Diagram

Stock No.	A	B	C	D
#47-625	5mm	5mm	3.5mm	7.1mm
#47-806				
#47-213				
#47-807	10mm	10mm	7.1mm	14.1mm
#49-418				
#49-421				
#49-419	15mm	15mm	10.5mm	21.2mm
#49-422				
#47-214				
#47-808	20mm	20mm	14.2mm	28.3mm
#47-626				
#47-809				
#49-420	50mm	50mm	35.4mm	70.7mm
#49-423				



COATING CURVES

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
