

[See all 10 Products in Family](#)

## TECHSPEC® 1:1 with 50mm and 50mm EFL Achromats, NIR Achromatic Pair



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock #47-298 [CONTACT US](#)

⊖ 1 ⊕ £219<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-5    | £219.20 each                  |
| Qty 6-25   | £175.20 each                  |
| Qty 26-49  | £169.60 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Relay Lens **Type:**

#### Physical & Mechanical Properties

22.0 **Clear Aperture CA (mm):**

**Center Air Spacing (mm):**

Housing Diameter (mm):  
30.0 +0.0/-0.10

Housing Length (mm):  
34.00 ±0.2

Image Distance (mm):  
39.72

Construction:  
Achromat Pair in Anodized Aluminum Housing

## Optical Properties

Substrate:   
N-LAK22 / N-SF6 / N-LAK22 / N-SF6

Surface Quality:  
40-20

Working f#:  
f/2.25

Coating:  
NIR II (750-1550nm)

Coating Specification:  
R<sub>abs</sub> ≤1.5% @ 750 - 800nm  
R<sub>abs</sub> ≤1.0% @ 800 - 1550nm  
R<sub>avg</sub> ≤0.7% @ 750 - 1550nm

Effective Focal Length EFL A (mm):  
50.00

Effective Focal Length EFL B (mm):  
50.00

Magnification:  
1:1

Object Distance (mm):  
39.72

Wavelength Range (nm):  
750 - 1550

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- 30mm Diameter Package Designed for NIR Applications
- Optimized for Various Magnification Ratios
- Ideal for Integration into OEM Applications
- NIR II Coated for 750-1550nm

Our 15.0mm and 30.0mm Mounted Achromatic Pairs combine our popular TECHSPEC® achromats into common configurations used for relay and projection applications. Packaged in a slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. Each lens has also been oriented for optimum system performance. All lenses AR coated. Lower f# pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

## Technical Information

