

[See all 6 Products in Family](#)

# 110mm Travel, Ultra Precision Linear Motor Stage, Integrated Controller, Linear Encoder

See More by [Zaber™](#)



Stock #70-564 **2 In Stock**

⊖ 1 ⊕ £7,400<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£7,400.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Metric **Type:**

Yes **Encoder:**

Yes **Manual Control/ LED Indicators:**

Zaber Technologies Inc. **Manufacturer:**

**Note:**

Requires a 24-48 VDC power supply and either [#15-295](#) for USB connectivity or [#15-297](#) for RS-232 connectivity. A data cable ([#15-296](#) or [#15-299](#)) can be used to daisy chain multiple stages together to control simultaneously.

**Type of Motor:**

Moving Magnet Track Linear Motor

**Encoder Type:**

Linear Analog Encoder

**Physical & Mechanical Properties****Type of Movement:**

Linear (X)

**Guide System:**

Crossed-Roller Bearing

**Stage Size (mm):**

245 x 151.5

**Travel (mm):**

110

**Accuracy (µm):**

1

**Height (mm):**

44

**Load Capacity (kg):**

12

**Repeatability (µm):**

<0.08

**Speed (mm/s):**

0.00061 - 1200

**Weight (kg):**

3.76

**Electrical****Maximum Operating Current (mA):**

3000

**Hardware & Interface Connectivity****Type of Drive:**

Moving Magnet Track Linear Motor

**Power Supply:**

Power Supply Required and Sold Separately.

USA: [#70-960](#)

Europe: [#70-960](#)

Japan: [#23-662](#)

Korea: [#33-773](#)

China: [#70-960](#)

**Computer Interface:**

RS-232

**Environmental & Durability Factors****Operating Temperature (°C):**

10 - 40

**Regulatory Compliance****RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 247:**

[Compliant](#)

**Product Details**

- 60, 110, 210mm Travel Options
- Up to 1200mm/s Speed
- Ultra-High Repeatability and Accuracy

Zaber™ Ultra High Precision Linear Motorized Stages are computer-controlled linear stages that utilize a moving magnet track linear motor and centrally located encoder to accurately and precisely position optical components or subsystems. These stages can connect directly to a computer's USB or RS-232 port and are compatible with [Zaber Launcher](#) and [Zaber's Motion Library](#) for quick set up and intuitive automation and control. The linear analog encoder has 1nm count size ensuring 1µm positional accuracy, < 0.08µm repeatability, and consistent minimal incremental movement steps down to 20nm. Zaber™ Ultra High Precision Linear Motorized Stages are driven by non-cogging ironless linear motors which allow for speeds up to 1200mm/s with a minimum speed and speed resolution of 0.61mm/s. These stages are designed with metric tapped holes for mounting and an indexed knob and push switch for manual control when needed.