

TECHSPEC® 1175nm 50mm Diameter, OD 2.0 Shortpass Filter



TECHSPEC OD 2.0 Shortpass Filters

Stock #67-292 CLEARANCE **20+ In Stock**

⊖ 1 ⊕ £172.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | £172.00 each |
| Qty 6-25 | £155.20 each |
| Qty 26-49 | £147.20 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Shortpass Filter **Type:**

Physical & Mechanical Properties

50.00 +0.0/-0.2 **Diameter (mm):**

Thickness (mm):

5.00 ±0.1

Clear Aperture (%):

80.00

Optical Properties

Angle of Incidence (°):

0

Optical Density OD (Average):

≥2.0

Cut-Off Wavelength (nm):

1,175.00

Substrate:

[Fused Silica](#) (Corning 7980)

Coating:

Traditional Coated

Rejection Wavelength (nm):

1265 - 1540

Surface Quality:

40-20

Transmission (%):

>85

Transmission Wavelength (nm):

550 - 1125

Transmitted Wavefront, P-V:

λ/4

Slope Factor (%):

±3

Cut-Off Tolerance (%):

±2

Wavelength Range (nm):

550 - 1540

Regulatory Compliance

Reach 224:

[Compliant](#)

Certificate of Conformance:

[View](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Sharp Cut-Off Wavelength
- High Transmission / Rejection Efficiency
- Precision Fused Silica Substrate

Our TECHSPEC® OD 2.0 Shortpass Filters are designed to have a very sharp transition from transmission to reflection, making them extremely useful in several applications. With an average transmission of 85% and an average blocking optical density of 2.0, excellent contrast can be achieved in machine vision and gauging applications. Available in a variety of cut-off wavelengths, they are ideal for fluorescence applications, separating spectral orders, and creating custom, efficient bandpass filters when combined with [TECHSPEC® OD 2.0 Longpass Filters](#). TECHSPEC® OD 2.0 Shortpass Filters have a single layer of AR coating on the back surface that enhances the overall efficiency of each filter. These filters are designed with a precision fused silica substrate.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Technical Information



Compatible Mounts