

[See all 10 Products in Family](#)

**TECHSPEC® 1:2.14 with 35mm and 75mm EFL Achromats, NIR Achromatic Pair**



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock **#47-296** [CONTACT US](#)

⊖ 1 ⊕ £219<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £219.20 each                  |
| Qty 6-25       | £175.20 each                  |
| Qty 26-49      | £169.60 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Relay Lens **Type:**

**Physical & Mechanical Properties**

22.0 **Clear Aperture CA (mm):**

**Center Air Spacing (mm):**

Housing Diameter (mm):  
30.0 +0.0/-0.10

Housing Length (mm):  
34.00 ±0.2

Image Distance (mm):  
64.24

Construction:  
Achromat Pair in Anodized Aluminum Housing

## Optical Properties

Substrate:   
N-LAK22 / N-SF6 / N-LAK22 / N-SF6

Surface Quality:  
40-20

Working f#:  
f/3.37

Coating:  
NIR II (750-1550nm)

Coating Specification:  
R<sub>abs</sub> ≤1.5% @ 750 - 800nm  
R<sub>abs</sub> ≤1.0% @ 800 - 1550nm  
R<sub>avg</sub> ≤0.7% @ 750 - 1550nm

Effective Focal Length EFL A (mm):  
35.00

Effective Focal Length EFL B (mm):  
75.00

Magnification:  
1:2.14

Object Distance (mm):  
25.00

Wavelength Range (nm):  
750 - 1550

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- 30mm Diameter Package Designed for NIR Applications
- Optimized for Various Magnification Ratios
- Ideal for Integration into OEM Applications
- NIR II Coated for 750-1550nm

Our 15.0mm and 30.0mm Mounted Achromatic Pairs combine our popular TECHSPEC® achromats into common configurations used for relay and projection applications. Packaged in a slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. Each lens has also been oriented for optimum system performance. All lenses AR coated. Lower f# pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

## Technical Information

