

**TECHSPEC® 12.5 x 25mm EFL Steinheil Triplet Achromatic Lens**



Stock #47-675 **20+ In Stock**

- 1 + £110.<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£110.40 each
Qty 6-25	£88.00 each
Qty 26-49	£83.20 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Achromatic Triplet Lens **Type:**

**Physical & Mechanical Properties**

12.50 +0.0/-0.025 **Diameter (mm):**

<3 **Centering (arcmin):**

18.00	Center Thickness CT (mm):
10.00	Center Thickness A (mm):
4.00	Center Thickness B (mm):
-15.65	Radius R <sub>4</sub> (mm):
15.39	Edge Thickness ET (mm):
Protective as needed	Bevel:

## Optical Properties

25.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
17.82	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
15.65	Radius R <sub>1</sub> (mm):
8.22	Radius R <sub>2</sub> (mm):
-8.22	Radius R <sub>3</sub> (mm):
<a href="#">N-BASF64 / N-BK7 / N-BASF64</a>	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
2.00	f#:
0.25	Numerical Aperture NA:
MgF <sub>2</sub> (400-700nm)	Coating:
R <sub>avg</sub> ≤ 1.75% @ 400 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
400 - 700	Wavelength Range (nm):

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 219:
<a href="#">View</a>	Certificate of Conformance:

### Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Designed for 1:1 Conjugate Ratios
- Ideal for Relay Systems
- [Hastings Triplet Achromatic Lenses](#) Also Available

TECHSPEC® Steinheil Triplet Achromatic Lenses are designed for 1:1 conjugate ratios and utilize symmetry to correct for aberrations. Steinheils are made from a low index center element cemented between two identical high index outer elements. Each lens is edged down to f-numbers with reasonable aberration correction at increased fields. TECHSPEC® Steinheil Triplet Achromatic Lenses feature small diameters that allow for mounting in smaller spaces

compared to traditional Steinheil lens designs. Steinheil Triplets are ideal for use in relay systems.

## Technical Information



## Coating Curves

;