

TECHSPEC[®] 12.5mm Dia., 3.00mm Thick, 532nm, λ/10 Fused Silica Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#48-208** **7 In Stock**

-

1

+

£118¹⁹

ADD TO CART

Volume Pricing	
Qty 1-5	£118.19 each
Qty 6-25	£94.55 each
Qty 26-49	£88.43 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Laser Line Window

Type:




Glass		Type of Window:
Physical & Mechanical Properties		
11.25	Clear Aperture CA (mm):	
12.50 +0.00/-0.10	Diameter (mm):	
3.00 ±0.10		Thickness (mm):
Protective as needed		Bevel:
90		Clear Aperture (%):
≤5		Parallelism (arcsec):
Fine Ground		Edges:
Optical Properties		
0		Angle of Incidence (°):
Laser V-Coat (532nm)		Coating:
532		Design Wavelength DWL (nm):
Fused Silica Eximer Grade (Corning 7980 KrF)		Substrate: ☐
1.458		Index of Refraction (n _d):
10-5		Surface Quality:
λ/10		Transmitted Wavefront, P-V:
67.8		Abbe Number (v _d):
R _{abs} <0.25% @ 532nm		Coating Specification:
10 J/cm² @ 532nm, 20ns, 20Hz		Damage Threshold, By Design: ☐
10 J/cm² @ 532nm, 20ns, 20Hz		Damage Threshold, Pulsed:
Material Properties		
7980 KrF 0A		Fused Silica Grade:
Regulatory Compliance		
Compliant		RoHS 2015:
Compliant		REACH 201:
View		Certificate of Conformance:

PRODUCT DETAILS

- 10-5 Surface Quality
- Damage Thresholds at Design Wavelengths
- Diameters from 12.5 to 76.2mm Available
- [Uncoated Substrates Available](#)

TECHSPEC® λ/10 Laser Line Coated Windows are designed for direct integration into laser applications. This robust product family features common imperial sizes, many of which offer multiple thickness options. Anti-reflection coatings are available at common laser wavelengths, minimizing surface reflection for optimal system transmission. TECHSPEC λ/10 Laser Line Coated Windows provide laser grade specifications including λ/10 surface flatness, 10-5 surface quality, and <3 arcmin parallelism. These windows are ideal for industrial laser applications ranging from protective coverings to separating various environments.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS