


TECHSPEC® 12.5mm Dia., 3mm Thick, VIS-NIR Coated,  $\lambda/4$  Fused Silica Window



TECHSPEC®  $\lambda/4$  UV Fused Silica Windows

Stock **#14-985** **1 In Stock**

-

1

+

£113<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £113.60 each                  |
| Qty 6-25       | £90.40 each                   |
| Qty 26-49      | £84.80 each                   |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

|       |           |
|-------|-----------|
| 32.00 | #Sorting: |
|-------|-----------|

General

|                   |       |
|-------------------|-------|
| Protective Window | Type: |
|-------------------|-------|

Physical & Mechanical Properties

|                         |
|-------------------------|
| Clear Aperture CA (mm): |
|-------------------------|

|                      |                             |
|----------------------|-----------------------------|
| 11.25                |                             |
|                      | Diameter (mm):              |
| 12.50 +0.00/-0.10    |                             |
|                      | Thickness (mm):             |
| 3.00 ±0.10           |                             |
|                      | Parallelism (arcmin):       |
| <1                   |                             |
|                      | Dimensional Tolerance (mm): |
| +0.00/-0.10          |                             |
|                      | Bevel:                      |
| Protective as needed |                             |
|                      | Clear Aperture (%):         |
| 90                   |                             |
|                      | Edges:                      |
| Fine Ground          |                             |
|                      | Poisson's Ratio:            |
| 0.16                 |                             |
|                      | Young's Modulus (GPa):      |
| 73                   |                             |
|                      | Knoop Hardness (kg/mm²):    |
| 522.00               |                             |

|                                                                                                                    |                                                       |
|--------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Optical Properties                                                                                                 |                                                       |
|                                                                                                                    | Coating:                                              |
| VIS-NIR (400-1000nm)                                                                                               |                                                       |
|                                                                                                                    | Substrate: <input type="checkbox"/>                   |
| Fused Silica (Corning 7980)                                                                                        |                                                       |
|                                                                                                                    | Index of Refraction (n <sub>d</sub> ):                |
| 1.458                                                                                                              |                                                       |
|                                                                                                                    | Surface Quality:                                      |
| 40-20                                                                                                              |                                                       |
|                                                                                                                    | Transmitted Wavefront, P-V:                           |
| λ/4                                                                                                                |                                                       |
|                                                                                                                    | Abbe Number (v <sub>d</sub> ):                        |
| 67.8                                                                                                               |                                                       |
|                                                                                                                    | Coating Specification:                                |
| R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm |                                                       |
|                                                                                                                    | Wavelength Range (nm):                                |
| 400 - 1000                                                                                                         |                                                       |
|                                                                                                                    | Damage Threshold, Reference: <input type="checkbox"/> |
| 5 J/cm² @ 532nm, 10ns                                                                                              |                                                       |

|                                                                   |                                                              |
|-------------------------------------------------------------------|--------------------------------------------------------------|
| Material Properties                                               |                                                              |
|                                                                   | Density (g/cm³):                                             |
| 2.20                                                              |                                                              |
|                                                                   | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) |                                                              |
|                                                                   | Fused Silica Grade:                                          |
| 7980 0G                                                           |                                                              |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
|                       | RoHS 2015:                  |
| Compliant             |                             |
|                       | Certificate of Conformance: |
| View                  |                             |
|                       | REACH 241:                  |
| Compliant             |                             |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Available Uncoated or BBAR Coated for UV, Visible, and NIR
- Ideal for Imaging Applications
- Circular and Rectangular Sizes from 5 to 200mm
- 1λ or λ/10 UV Fused Silica Windows Also Available


TECHSPEC® λ/4 UV Fused Silica Windows are manufactured with 40-20 surface quality and λ/4 transmitted wavefront error specifications, making them ideal for imaging applications. Featuring UV fused silica substrates, these windows provide high transmission from the ultraviolet (UV) through the visible and near-infrared (NIR). Broadband anti-reflection (BBAR) coating options are available to minimize reflection losses and increase transmission. TECHSPEC λ/4 UV Fused Silica Windows are used in optical imaging applications, in low to medium powered laser applications, and as protective windows, especially in applications requiring transmission of UV light.

Technical Information



FUSED SILICA


Uncoated Fused Silica  
Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

Fused Silica with MgF<sub>2</sub> Coating  
Typical Transmission







Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.





The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700nm$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

|                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>Wavelength (nm)</div> <div><div>Fused Silica with UV-AR Coating<br/>Typical Transmission</div><div></div></div> | <div>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:<div><div><math>R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}</math></div><div><math>R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}</math></div><div><math>R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}</math></div></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |
| <div>Fused Silica with UV-VIS Coating<br/>Typical Transmission</div> <div></div>                                    | <div>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:<div><div><math>R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}</math></div><div><math>R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}</math></div></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                         |
| <div>Fused Silica with VIS-EXT Coating<br/>Typical Transmission</div> <div></div>                                  | <div>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:<div><div><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                                |
| <div>Fused Silica with VIS-NIR Coating<br/>Typical Transmission</div> <div></div>                                  | <div>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:<div><div><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math></div><div><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math></div><div><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |
| <div>Fused Silica with VIS 0° Coatina</div>                                                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |

|                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Typical Transmission</div></div>                                         | <p>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                        |
| <div><div>Fused Silica with YAG-BBAR Coating<br/>Typical Transmission</div></div> | <p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math><br/><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>           |
| <div><div>Fused Silica with NIR I Coating<br/>Typical Transmission</div></div>   | <p>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                     |
| <div><div>Fused Silica with NIR II Coating<br/>Typical Transmission</div></div>  | <p>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.5\% @ 750 - 800\text{nm}</math><br/><math>R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}</math><br/><math>R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

Coating Curves

# Compatible Mounts

;