

[See all 4 Products in Family](#)

12.7mm Dia. x 25.4mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens | CF-BX-12-25

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#24-763** CLEARANCE **1 In Stock**

-

1

+

£116^{.80}

ADD TO CART

Volume Pricing	
Qty 1-9	£116.80 each
Qty 10+	£105.60 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Double-Convex Lens

Model Number:

CF-BX-12-25

Physical & Mechanical Properties

12.70 +0.00/-0.13	Diameter (mm):
<3	Centering (arcmin):
Protective as needed	Bevel:
3.60 ±0.20	Center Thickness CT (mm):
1.50	Edge Thickness ET (mm):
11.43	Clear Aperture CA (mm):

Optical Properties	
25.40 @ 5μm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate: ☐
60-40	Surface Quality:
λ	Irregularity (P-V) @ 632.8nm:
19.77	Radius R ₁ (mm):
19.77	Radius R ₂ (mm):
2.00	f/#:
±2	Focal Length Tolerance (%):
0.25	Numerical Aperture NA:
300 - 8000	Wavelength Range (nm):


Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:



Product Details

- Greater than 90% Transmission from 350nm-7μm
- Low Index of Refraction
- High Laser Damage Threshold

ISP Optics Calcium Fluoride Double-Convex(DCX) Lenses are ideal for finite imaging applications requiring high transmission in the infrared wavelength spectrum. Calcium Fluoride features greater than 90% transmission from 350nm to 7μm and a low refractive index, allowing it to be used without an antireflective coating. In addition, its low absorption and high damage threshold makes it a popular choice for use with excimer lasers. ISP Optics Calcium Fluoride Double-Convex(DCX) Lenses offer low solubility and superior hardness compared to other fluoride-based substrates, allowing for use in harsh environments.

Technical Information





Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools