

[See all 2 Products in Family](#)

13.5nm, 25.4mm Dia, 45° AOI, EUV Flat Mirror



Extreme Ultraviolet (EUV) Flat Mirrors

Stock **#38-760** **20+ In Stock**

⊖ 1 ⊕ £2,200⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£2,200.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

25.40 ±0.25 **Diameter (mm):**

Commercial Polish **Back Surface:**

Clear Aperture (%):

Edges:

Fine Ground

Parallelism (arcmin):

3

Surface Roughness (\square):

<5 RMS

Thickness (mm):6.35 \pm 0.508**Optical Properties****Surface Flatness (P-V):** $\lambda/10$ @ 632.8nm**Substrate:** \square

Single Crystal Silicon

Surface Quality:

10-5

Coating Specification: $R_{\text{abs}} >65\%$ @ 13.5nm, 45° (s-pol)**Coating:**Mo/Si Multilayer
Top Layer: Silicon**Coating Type:**

Metal/Semiconductor

Angle of Incidence (°):

45

Design Wavelength DWL (nm):

13.5

Wavelength Range (nm):

12.92 - 13.90

Full Width-Half Max FWHM (nm):

0.98

Reflection at DWL (%):

>65

Electrical**Center Energy (eV):**


92

Regulatory Compliance**Certificate of Conformance:**[View](#)**Product Details**

- Maximum Achievable Reflection at 13.5nm
- Designed for EUV Beam Steering and Harmonic Separation
- 5° and 45° AOI Versions Available

Extreme Ultraviolet (EUV) Flat Mirrors are multilayer mirrors designed for maximum achievable reflectance at the design wavelength and angle of incidence. These mirrors feature a coating deposited on a super-polished single crystal silicon substrate and surface roughness less than 3 \square RMS. The 45° AOI mirrors are useful for steering s-polarized beams, while the 5° AOI mirrors may be used with unpolarized beams. Applications for EUV mirrors include Coherent Diffractive Imaging (CDI) and materials science research. Extreme Ultraviolet (EUV) Flat Mirrors can also serve as harmonic selectors for High Harmonic Generation (HHG) beams.

Note: Test data from each mirror's production run sample included.

Technical Information**Compatible Mounts**

