

[See all 10 Products in Family](#)

## 150 x 150mm UV Polarizing Film



Stock **#25-108** [CONTACT US](#)

⊖ 1 ⊕ £664.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£664.00 each
Qty 10-25	£531.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Linear Polarizer

**Type:**

Protective Film on Both Sides

**Note:**

### Physical & Mechanical Properties

150.00

**Length (mm):**

150.0 x 150.0 ±0.2	<b>Dimensions (mm):</b>
0.19 Nominal	<b>Thickness (mm):</b>
Polarizing Film	<b>Construction:</b>
150.00	<b>Width (mm):</b>

## Optical Properties

Uncoated	<b>Coating:</b>
1000:1 (avg @ 325nm-400nm) 6000:1 (avg @ 400nm-750nm)	<b>Extinction Ratio:</b>
CTA (Cellulose Triacetate)	<b>Substrate:</b> <input type="checkbox"/>
320 - 750	<b>Wavelength Range (nm):</b>
39 (325nm-400nm)	<b>Transmission, Single (%):</b>
0.04 (325nm-400nm)	<b>Transmission, Crossed (%):</b>

## Environmental & Durability Factors

Heat Resistance: 70°C dry Cold Resistance: -20°C	<b>Operating Temperature (°C):</b>
DIN ISO 9022-2-10-04 DIN ISO 9022-2-11-05 DIN ISO 9022-2-12-07 DIN ISO 9022-2-14-02	<b>Environmental Durability:</b>
15 - 25	<b>Storage Temperature (°C):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 253:</b>

## Product Details

- High UV Transmission from 325 - 400nm
- 1000:1 Contrast From 325 - 400nm, 6000:1 Contrast From 400 - 750nm
- Thin, Versatile Polymer Substrate

Ultraviolet (UV) Linear Polarizing Film provides excellent contrast, and transmission up to 39% for P-Polarized Light in the UV and VIS ranges from 325-750nm. A range of rectangular sizes are available to accommodate small and large beam diameters as well as LED light sources. Ultraviolet (UV) Linear Polarizing Films are made with a durable, robust film substrate that is flexible and can be cut to size using scissors. This polarizing film is a cost-effective alternative to glass UV polarizers, and are ideal for use in industrial sensing, spectroscopy, and microscopy applications. [Near-Infrared \(NIR\) Linear Polarizing Film](#) and Visible [TECHSPEC High Contrast Linear Polarizing Film \(XP42\)](#) are also available.