

TECHSPEC[®] 15.0mm Dia x 3mm Thick 532/1064nm, Zerodur Dual Band Laser Mirror



Stock **#29-057** 9 In Stock

-

1

+

£148^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	£148.80 each
Qty 6-25	£130.40 each
Qty 26-49	£116.80 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

15.00 +0.00/-0.20

Diameter (mm):

Commercial Polish

Back Surface:

Protective as needed	Bevel:
90	Clear Aperture (%):
30	Parallelism (arcsec):
3.00 ±0.20	Thickness (mm):

Ground	Edges:
--------	--------

Optical Properties

532, 1064	Design Wavelength DWL (nm):
-----------	-----------------------------

ZERODUR®	Substrate: ☐
----------	-------------------------------------

Laser Mirror (532, 1064nm)	Coating:
----------------------------	----------

Rabs >99.5% @ 532 & 1064nm	Coating Specification:
----------------------------	------------------------

Dielectric	Coating Type:
------------	---------------

20-10	Surface Quality:
-------	------------------

15 J/cm2 @ 20ns @ 532nm 20 J/cm2 @ 20ns @ 1064nm	Damage Threshold, By Design: ☐
--	---

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- >99.5% Reflectivity at Design Wavelengths
- Low Coefficient of Thermal Expansion
- 532/1064nm or 635/670/1064nm Wavelength Bands

TECHSPEC® Zerodur® Dual Band Laser Line Mirrors feature high reflectivity coatings with either two or three wavelength bands on a durable Zerodur® substrates. The ZERODUR® substrates have a low coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® Zerodur® Dual Band Laser Line Mirrors are available in a highly reflective 532/1064nm or 635/670/1064nm dual band coatings and multiple standard diameter options for Nd:YAG lasers and red and green guide beams. These mirrors are ideal for beam steering applications in both laboratory and OEM laser systems.