

# UV 365nm, MicroBrite Ultra High Intensity Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination MicroBrite Ultra High Intensity Bar Light

Stock **#18-544** 2 In Stock

-

1

+

£1,040<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £1,040.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                                                                                                                     |                       |
|-----------------------------------------------------------------------------------------------------------------------------|-----------------------|
| AL295-1503651C                                                                                                              | Model Number:         |
| 50,000                                                                                                                      | LED Lifetime (hours): |
| LED Illuminator                                                                                                             | Type of Illumination: |
| <div>Note:<br/>Optional Manual Intensity Adjustment <a href="#">#86-887</a> and <a href="#">#89-555</a> are Available</div> |                       |

|                                                                                                                                                                                                                                                                        |                             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Advanced Illumination                                                                                                                                                                                                                                                  | Manufacturer:               |
| Bar Light                                                                                                                                                                                                                                                              | Geometry:                   |
| Constant                                                                                                                                                                                                                                                               | Illumination Mode:          |
| Physical & Mechanical Properties                                                                                                                                                                                                                                       |                             |
| 165.6 x 20.1 x 20.1                                                                                                                                                                                                                                                    | Dimensions (mm):            |
| 68.9                                                                                                                                                                                                                                                                   | Weight (g):                 |
| Optical Properties                                                                                                                                                                                                                                                     |                             |
| UV                                                                                                                                                                                                                                                                     | Color:                      |
| 365                                                                                                                                                                                                                                                                    | Wavelength (nm):            |
| Electrical                                                                                                                                                                                                                                                             |                             |
| 0.15A                                                                                                                                                                                                                                                                  | Maximum Input Current:      |
| Hardware & Interface Connectivity                                                                                                                                                                                                                                      |                             |
| Flying Leads                                                                                                                                                                                                                                                           | Connector:                  |
| 24V                                                                                                                                                                                                                                                                    | Input Voltage (V):          |
| <div>Power Supply Required and Sold Separately.</div> <div>USA: <a href="#">#66-855</a></div> <div>Europe: <a href="#">#66-855</a></div> <div>Japan: <a href="#">#89-513</a></div> <div>Korea: <a href="#">#33-773</a></div> <div>China: <a href="#">#66-855</a></div> |                             |
| Environmental & Durability Factors                                                                                                                                                                                                                                     |                             |
| 0 - 60                                                                                                                                                                                                                                                                 | Operating Temperature (°C): |
| IP50                                                                                                                                                                                                                                                                   | Environmental Rating:       |
| Regulatory Compliance                                                                                                                                                                                                                                                  |                             |
| <a href="#">Exempt</a>                                                                                                                                                                                                                                                 | RoHS 2015:                  |
| <a href="#">View</a>                                                                                                                                                                                                                                                   | Certificate of Conformance: |
| <a href="#">Contains SVHC(s)</a>                                                                                                                                                                                                                                       | Reach 233:                  |


## Product Details

- High Intensity Output up to 73,000 Lux
- Compact Housing with T-Slot Mount
- Full Range of Wavelengths Available
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Advanced Illumination MicroBrite Ultra High Intensity Bar Lights offer high performance machine vision lights in a compact form factor. With a high intensity output of 73,000 Lux at a working distance of 100mm, these MicroBrite Bar Lights outperform higher cost comparable bar lights. These bar lights are available in the most common machine vision wavelengths. Advanced Illumination MicroBrite Ultra High Intensity Bar Lights are designed for applications requiring intense illumination for large area inspection. Please contact us if your application requires a MicroBrite Ultra High Intensity Bar Light with a custom length.

**Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.

3D-Printable Mount Files



Bar or Line Light Configuration

**DOWNLOAD  
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications  
[Read](#)



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries  
[Watch](#)