


TECHSPEC[®] 15mm Square Uncoated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock **#64-086** [CONTACT US](#)

-

1

+

£28²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£28.20 each
Qty 6-25	£22.40 each
Qty 26-99	£20.80 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

21.00

#Sorting:

General

Protective Window

Type:

Physical & Mechanical Properties

13.50 x 13.50	Clear Aperture CA (mm):
15.00 x 15.00	Dimensions (mm):
2.00	Thickness (mm):
15.00	Length (mm):
15.00	Width (mm):
±0.25	Dimensional Tolerance (mm):
Protective as needed	Bevel:
Fine Ground	Edges:
0.22	Poisson's Ratio:
71.5	Young's Modulus (GPa):
500.00	Knoop Hardness (kg/mm ²):

Optical Properties	
Uncoated	Coating:
B270	Substrate: □
1.523	Index of Refraction (n _d):
60-40	Surface Quality:
58.3	Abbe Number (v _d):
360 - 2700	Wavelength Range (nm):
1λ	Surface Flatness (P-V):

Material Properties	
2.56	Density (g/cm ³):
9.4 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Large Selection of Sizes
- Available Uncoated, MgF2, or VIS-NIR Anti-Reflection (AR) Coated
- Custom Sizes Available for Volume OEM Requirements

TECHSPEC® B270 Windows offer a high transmission from the visible to the near-infrared (NIR). They have a similar refractive index to N-BK7 while being more cost-effective. These windows are often used as a protective element due to their high solarization stability and chemical resistance, making them ideal for standard window applications. TECHSPEC® B270 Windows are available either uncoated or coated with a MgF2 or VIS-NIR Anti-Reflection (AR) Coating. Both circular and square options are offered in various sizes, and custom sizes and coatings are available for OEM applications.

Technical Information



Compatible Mounts

;