

# 1.61mm<sup>2</sup> Four-Element UV Enhanced Segmented Photodiode



Stock **#84-613** **2 In Stock**

£72.<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1-4	£72.00 each
Qty 5-9	£63.60 each
Qty 10-24	£55.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### General

10.00 **Rise Time (ns):**  
SPOT-4DUV **Model Number:**

#### Physical & Mechanical Properties

1.3x1.3 **Size of Active Area (mm):**

1.61	<b>Active Area (mm<sup>2</sup>):</b>
0.127	<b>Element Gap (mm):</b>
<b>Electrical</b>	
Minimum: 0.08 Typical: 0.1	<b>Responsivity @ 970nm (AW):</b>
40.00	<b>Capacitance @ V<sub>R</sub>=-10V (pF):</b>
1.3 x 10 <sup>-13</sup>	<b>Noise Equivalent Power NEP (W/ Hz<sup>1/2</sup>):</b> @ -10 V, 970nm
5.00	<b>Maximum Reverse Voltage (V):</b>
Maximum: 500 Typical: 100	<b>Dark Current @ V<sub>R</sub>=-10V (nA):</b>
<b>Hardware &amp; Interface Connectivity</b>	
41 / TO-5	<b>Connector:</b>
<b>Environmental &amp; Durability Factors</b>	
-10 to 60	<b>Operating Temperature (°C):</b>
-20 to 70	<b>Storage Temperature (°C):</b>
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- High Stability Over Temperature and Time
- Excellent Resolution, High Accuracy, Ultra-Low Dark Current
- Two or Four Separate Active Area Segments
- [Segmented InGaAs Photodiodes](#) Also Available

Segmented Photodiodes are designed for a wide variety of applications that require high stability and fast response times. Featuring position resolutions of greater than 0.1µm, Segmented Photodiodes are ideal for surface profiling, position measurement, alignment, or targeting. Segmented Photodiodes are segmented into either two or four separate active areas and have spectral response ranges from 350 – 1100nm. The segmented regions allow various measurement profiles on a single detector.