

[See all 21 Products in Family](#)

1.8 - 3.0mm FL C-Mount, Manual Iris, Wide Angle Lens



1.8 - 3.0mm FL C-Mount, Manual Iris, Wide Angle Lens, #89-524

Stock **#89-524** **1 In Stock**

⊖ 1 ⊕ £839⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£839.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Low Distortion Wide Angle Lenses **Series:**

Varifocal Lens **Type:**

Physical & Mechanical Properties

Variable **Iris Option:**

Length (mm):

45.00	
39.0	Maximum Diameter (mm):
39	Outer Diameter (mm):
70.00	Weight (g):

Optical Properties

105 - 77°	Horizontal Field of View, 1/3" Sensor:
7.40	Maximum Image Circle (mm):
1.80	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
f/1.8 - Closed	Aperture (f#):
<1	Distortion (%):
<1	Maximum Distortion (%):
VS	Lens Wavelength Range:

Sensor

1/2.3"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

N/A	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.