

20.0mm Beam Steering Assembly



#67-363

Stock **#67-363** **3 In Stock**

⊖ 1 ⊕ £372.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	£372.80 each
Qty 11+	£347.28 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Adjustable - Beam Steering

Type:

Circular

Type of Optics:

360° Horizontal, 6° Tilt

Range:

Physical & Mechanical Properties

Construction:
Black Anodized Aluminum & Stainless Steel

Post Diameter (mm):
20.0

Threading & Mounting

Size of Compatible Optics (mm):
25.0 - 25.4

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Ready to Use Beam Steering Assembly
- High Resolution 100 TPI Kinematic Mounts
- Available with 20mm Post for Higher Stability

Beam Steering Assemblies are specifically suited for numerous applications in laser holography, interferometry and other exacting set-ups and systems requiring precise redirection of an optical beam. The 12.7mm Beam Steering Assembly comprises a slotted base, suitable for attachment to metric and imperial bench plates, a main 300mm post and two 100 TPI kinematic mounts with 6° tilt range, suitable for 1" or 25mm diameter optics. The kinematic mounts can be moved vertically and can also be rotated 360° around the main post. The 20mm Beam Steering Assembly is designed for applications that require a higher level of stability and feature a larger slotted base than its 12.7mm counterpart; it includes a 20mm main post and heavy duty cross clamps. Mirrors are held in place with an #8 set screw.

Technical Information

