

[See all 23 Products in Family](#)

TECHSPEC[®]

20mm Dia., Vacuum UV (VUV) Mirror



Precision Ultraviolet Mirrors

Stock **#18-728** **5 In Stock**

-

1

+

£248⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£248.80 each
Qty 6-25	£198.40 each
Qty 26-49	£186.40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

20.00 +0.0/-0.2

Diameter (mm):

Back Surface:

Commercial Polish	
90	Clear Aperture (%):
<30	Parallelism (arcsec):
Thickness (mm):	
3.00 ±0.20	

Optical Properties	
λ/10	Surface Flatness (P-V):
Substrate:	
Fused Silica (Corning 7980)	
20-10	Surface Quality:
Coating Specification:	
R _{avg} ≥78% @ 120 - 125nm	
R _{avg} ≥85% @ 120 - 600nm	
Coating:	
Enhanced Aluminum (120-600nm)	
Coating Type:	
Metal	
Angle of Incidence (°):	
0	
Design Wavelength DWL (nm):	
120	
Wavelength Range (nm):	
120 - 600	

Material Properties	
Vacuum Compatibility:	
10 ⁻⁷ Torr	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	


Product Details


- 120nm and 190nm Design Wavelengths
- Average Reflectivity >85% Across Specified Range
- Enhanced Metallic Coatings for Broadband Reflectivity through the Visible Region

TECHSPEC® Precision Ultraviolet Mirrors are ideal for most commercially available light sources and are offered in both Deep UV (DUV) and Vacuum UV (VUV) enhanced coating options. The DUV coating offers excellent reflection from 190nm to the long-wave infrared (LWIR), while the VUV coating has optimized reflection from 120nm to the LWIR. These mirrors are designed for 0° angle of incidence and feature an aluminum-based coating for low polarization sensitivity. TECHSPEC® Precision Ultraviolet Mirrors have an average reflectivity of greater than 85% across a specified range. The mirrors are available in diameters ranging from 5 to 50mm.

Note: The soft coating can be easily damaged by fingerprints and aerosols.

Technical Information





Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts