

[See all 12 Products in Family](#)

## 25 x 25mm UV Fused Silica Ground Glass Optical Diffuser



Stock #49-158 **20+ In Stock**

⊖ 1 ⊕ £51<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	£51.20 each
Qty 11-49	£40.80 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Ground Glass Diffuser **Type:**

### Physical & Mechanical Properties

25.00 x 25.00 **Dimensions (mm):**

220 **Grit:**

1.60 Thickness (mm):

25.00 Width (mm):

25.00 Length (mm):

## Optical Properties

Fused Silica (Corning 7980) Substrate:

200 - 2200 Wavelength Range (nm):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Even, Diffuse Surface
- Ideal for Applications Utilizing UV Wavelengths
- Low Scatter Loss
- [Float Glass Substrates](#) Also Available

UV Fused Silica Ground Glass Diffusers are comprised of high tolerance, quality ground glass, making them ideal for a variety of industrial applications. A 220-grit sandblast is used to create a diffuse surface on the UV fused silica substrate of these optical diffusers. Undergoing two orthogonal passes during this sandblast process yields an even diffusion across the surface. The scattering is a compromise of low scatter loss and medium diffusion. UV Fused Silica Ground Glass Diffusers are typically applied for use in screens, illuminator diffusion, and targets.

## Technical Information



## Compatible Mounts