

[See all 3 Products in Family](#)

25.4mm Dia. 5°, 800nm Highly-Dispersive Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) 800nm Highly-Dispersive Ultrafast Mirrors



Stock **#12-331** 12 In Stock

-

1

+

£612^{.00}

ADD TO CART

Volume Pricing	
Qty 1-3	£612.00 each
Qty 4-7	£544.00 each
Qty 8+	£476.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Model Number:

HD15

Physical & Mechanical Properties	
10 ±5	Wedge Angle (arcmin):
80	Clear Aperture (%):
Commercial Polish	Back Surface:
25.40 +0.0/-0.1	Diameter (mm):
6.35 ±0.20	Thickness (mm):
Optical Properties	
>99.9% (typical, p-polarization)	Reflection at DWL (%):
R _{avg} >99.8%, GDD = -1300 fs ² @ 780 - 830nm (p-polarization) R _{abs} >99.9% @ 800nm (typical, p-polarization)	Coating Specification:
-1300fs ² @ 780 - 830nm	GDD Specification:
780 - 830	Wavelength Range (nm):
λ/10	Irregularity (P-V) @ 632.8nm:
Dielectric	Coating Type:
Ultrafast (780-830nm)	Coating:
800	Design Wavelength DWL (nm):
5	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: ☐
0.3 J/cm ² @ 800nm, 50fs, 1kHz, 100µm Beam Diameter	Damage Threshold, By Design: ☐

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reflection >99.8% (P-polarization) at 720 – 840nm or 780 – 830nm
- Low Group Delay Dispersion at 5° or 20° AOIs
- Ideal for Pulse Compression of Ti:sapphire Ultrafast Lasers
- [Low GDD Mirrors](#) Also Available

UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors feature an optimized multilayer ultrafast chirped coating based on dispersive optical interference that provides a low group delay dispersion (GDD) and high reflectance. These ultrafast mirrors provide GDDs as low as -1300fs² and greater than 99.8% reflectivity for p-polarization. The highly-dispersive design of these ultrafast mirrors offers control of third and higher order dispersions, and provides high beam stability at either 5° or 20° angle of incidence. UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors are ideal for pulse compression and dispersion compensation of ultrafast pulses, such as Ti:sapphire lasers. Standard imperial sizes are available, featuring fused silica substrates.

Technical Information



Compatible Mounts

;