

25.4mm Clear Aperture, 30 Arcsec, Aluminum Retroreflector



Stock #46-175 **1 In Stock**

- 1 + £576.⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | £576.00 each |
| Qty 10-24 | £518.40 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Retroreflector **Type:**

Physical & Mechanical Properties

25.4 **Clear Aperture CA (mm):**

41.30 **Diameter (mm):**

Dimensional Tolerance (mm):

±1.6

Optical Properties

Beam Deviation (arcsec):
30.00

Coating:
Enhanced Aluminum (450-650nm)

Exiting Wavefront Accuracy:
3.5λ

Substrate: □
BOROFLOAT®

Surface Quality:
80-50

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Threading & Mounting

Mounting Threads:
(2) 1/4-20, M6 x 1.0

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant


Certificate of Conformance:
[View](#)

Product Details

- Incident Light is Reflected Back to the Source
- Hollow Lightweight Design
- No Material Absorption or Chromatic Aberration


Hollow Retroreflectors are constructed of three first surface mirrors assembled into a corner cube. This produces a lightweight "hollow corner cube" that is totally insensitive to position and movement. The result is that parallel incident light is reflected back to the source with great accuracy, regardless of the angle of incidence. Since the optical path is in air, this configuration eliminates material absorption and chromatic aberrations present in solid glass prism-type retroreflectors. The larger housings feature a variety of mounting holes on the back plate.

The specified beam deviation value of each Hollow Retroreflector is the maximum deviation from parallelism of any single return beam from any of the six sub-apertures, when the retroreflector is fully illuminated. Exiting wavefront is the resultant peak-to-valley wavefront deformation from a fully illuminated retroreflector, which is listed in factors of λ (where λ = 633nm). The unique, patented cushion mounting makes these Hollow Retroreflectors extremely resistant to shock.



Technical Information

| Clear Aperture (CA) | Diameter | L1 | L2 | A | B | C |
|---------------------|----------|----------|---------|---------|---------|-----------|
| 6.4mm | 8.1mm | 8.1mm * | — | — | — | — |
| 12.7mm | 14.6mm | 19.1mm * | — | — | — | M3 x 0.5 |
| 25.4mm | 41.3mm | 36.5mm | 49.2mm | 44.5mm | 50.8mm | 1/4-20 |
| 50.8mm | 76.2mm | 62.0mm | 79.5mm | 78.7mm | 94.2mm | 1/4-20 ** |
| 63.5mm | 89.4mm | 61.5mm | 79.0mm | 92.3mm | 101.6mm | 1/4-20 ** |
| 127.0mm | 166.7mm | 125.5mm | 150.8mm | 171.5mm | 221.9mm | 1/4-20 ** |



*Does not have back plate

**Additional 8 mounting holes on 50.8mm and larger Dia: (4) M6 x 1.0 at 90° and (4) 1/4-20 at 90° on 2" Bolt Circle

Coating Curves
