

TECHSPEC® 25.4mm Dia., 532 & 1064nm T, 266nm R 45° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock #11-546 **20+ In Stock**

⊖ 1 ⊕ £304⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£304.80 each
Qty 6-24	£274.40 each
Qty 25-49	£244.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Harmonic Beamsplitter **Type:**

Physical & Mechanical Properties

>90 **Clear Aperture (%):**

Construction:

Dichroic	
25.40 +0.00/-0.10	Diameter (mm):
<3	Parallelism (arcmin):
6.35 ±0.20	Thickness (mm):
Optical Properties	
45	Angle of Incidence (°):
Coating Specification:	
Surface 1: R _{abs} : >95% @ 266nm, T _{abs} : >98% @ 532nm, T _{abs} : >98% @ 1064nm	
Surface 2: R _{abs} : <1.0% @ 532nm, R _{abs} : <1.0% @ 1064nm	
266	Reflection Wavelength (nm):
Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>
M10	Surface Flatness (P-V):
10-5	Surface Quality:
532, 1064	Transmission Wavelength (nm):
Damage Threshold, By Design: <input type="checkbox"/>	
Surface 1:	
1 J/cm ² @ 266nm, 20ns, 20Hz	
5 J/cm ² @ 532nm, 20ns, 20Hz	
7.5 J/cm ² @ 1064nm, 20ns, 20Hz	
Surface 2:	
10 J/cm ² @ 20ns, 20Hz @ 532nm	
15 J/cm ² @ 20ns, 20Hz @ 1064nm	
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

Compatible Mounts

;