

[See all 44 Products in Family](#)

**TECHSPEC® 25.4mm Dia., 532nm T, 1064nm R 45° Thin Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock **#29-055** [CONTACT US](#)

⊖ 1 ⊕ £241<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £241.60 each                  |
| Qty 6-24       | £217.60 each                  |
| Qty 25-49      | £193.60 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Laser Window Substrate **Type:**

**Physical & Mechanical Properties**

90 **Clear Aperture (%):**

**Construction:**

Dichroic

25.40 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

3.18 ± 0.20 **Thickness (mm):**

## Optical Properties

45 **Angle of Incidence (°):**

**Coating Specification:**  
Surface 1: R<sub>abs</sub>: >99% @ 1064nm, T<sub>abs</sub>: >95% @ 532nm  
Surface 2: R<sub>abs</sub>: <0.5% @ 532nm

1064 **Reflection Wavelength (nm):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532 **Transmission Wavelength (nm):**

**Damage Threshold, By Design:**   
Surface 1:  
7.5 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz  
7.5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz  
Surface 2:  
10 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.