


25.4mm Dia. x 150mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) PCX Lens | CF-PX-25-150

See More by [ISP Optics](#)



Stock **#24-799** CLEARANCE **2 In Stock**

-

1

+

£169^{.81}

ADD TO CART

Volume Pricing	
Qty 1+	£169.81 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Plano-Convex Lens

Type:

CF-PX-25-150	Model Number:
Physical & Mechanical Properties	
25.40 +0.00/-0.13	Diameter (mm):
<3	Centering (arcmin):
3.40 ±0.20	Center Thickness CT (mm):
3.40	Edge Thickness ET (mm):
22.86	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
150.00 @ 5µm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate: □
60-40	Surface Quality:
λ	Irregularity (P-V) @ 632.8nm:
±2	Focal Length Tolerance (%):
59.98	Radius R ₁ (mm):
5.91	f/#:
0.08	Numerical Aperture NA:
300 - 8000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Greater than 90% Transmission from 0.35-7µm
 - Low Index of Refraction
 - Ideal for Integration into Infrared Systems
- ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses provide greater than 90% transmission from 350nm to 7µm and feature a low refractive index, allowing them to be used without an Anti-Reflection (AR) coating. Calcium Fluoride features a high laser damage threshold and low stress birefringence, making them highly suitable for integration into infrared systems. Additionally, calcium fluoride features low solubility and offers superior hardness to comparable fluoride-based substrates, making these PCX lenses capable of withstanding harsh environments and exposure to the elements. ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses are ideal for demanding applications that require superior performance from the visible through the mid-wave infrared (MWR) spectra.

SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools