


[See all 8 Products in Family](#)

TECHSPEC®

25.4mm Dia. x 25.4mm EFL, Enhanced Deep UV (DUV) 90° Off-Axis Mirror



Ultraviolet Off-Axis Parabolic (OAP) Mirrors

Stock #25-465 5 In Stock

-

1

+

£449⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£449.60 each
Qty 6-10	£360.00 each
Qty 11-25	£336.80 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Off-Axis Parabolic Mirror

Physical & Mechanical Properties

Y Offset (mm):

25.4

Diameter (mm):

25.40 +0.0/-0.1	
Surface Roughness (□):	
<50 RMS	
Optical Properties	
Coating Type:	
Metal	
Coating:	
Enhanced Aluminum (190-900nm)	
Off-Set Angle (°):	
90	
Wavelength Range (nm):	
190 - 900	
Effective Focal Length EFL (mm):	
25.40	
Substrate: □	
Aluminum 6061-T6	
Coating Specification:	
R _{avg} ≥92% @ 190 - 250nm R _{avg} ≥83% @ 250 - 900nm	
Focal Length Tolerance (%):	
±1	
Parent Focal Length PFL (mm):	
12.7	
Surface Figure, RMS:	
λ/8	
Surface Quality:	
80-50	
Radius of Curvature (mm):	
25.40	
Reflected Wavefront, RMS:	
λ/4	

Threading & Mounting	
Compatible Mounting Plates:	
#47-111	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	


Product Details

- Enhanced Metallic Coating for High Reflectivity Across Deep UV (DUV) and Visible Spectra
- 190nm Design Wavelength
- <50ÅRMS Surface Roughness

TECHSPEC® Ultraviolet Off-Axis Parabolic (OAP) Mirrors are coated with a DUV Enhanced Aluminum coating for excellent reflection from 190 – 900nm. To minimize scatter, these OAPs feature aluminum substrates and are diamond turned to have a surface roughness of <50ÅRMS. Standard imperial diameters are available with multiple focal length options which range from 25.4 – 203mm. TECHSPEC® Ultraviolet Off-Axis Parabolic Mirrors are ideal for use in DUV ellipsometers, DUV Raman spectroscopy, or for general focusing of UV light generated by broadband light sources. To facilitate mounting and system integration, threaded mounting plate [#47-111](#) (sold separately) which attaches to the base of these off-axis parabolic mirrors are available.

Note: The soft coating can be easily damaged by fingerprints and aerosols.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;