


25mm Dia., 1550nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock **#13-621** 1 In Stock

-

1

+

£1,320⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,320.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties	
25.00	Diameter (mm):
0.50 ±0.05	Thickness (mm):
±0.1	Dimensional Tolerance (mm):
480.00	Knoop Hardness (kg/mm²):

58.605	Young's Modulus (GPa):
0.21	Poisson's Ratio:
Optical Properties	
0 ±5	Angle of Incidence (°):
BBAR (1510-1590nm)	Coating:
1550	Design Wavelength DWL (nm):
>100,000:1	Extinction Ratio:
Borosilicate Glass Containing Elongated Silver Crystals	Substrate: ☐
>98.5	Minimum Transmission (%):
40-20	Surface Quality:
Ravg <0.25% @ 1510 - 1590nm	Coating Specification:
1510 - 1590	Wavelength Range (nm):
1.5051	Index of Refraction (n _d):
57.6	Abbe Number (v _d):
Hardware & Interface Connectivity	
<0.06	Insertion Loss (dB):
Material Properties	
6.5	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.412	Density (g/cm³):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Extinction Ratio and Low Insertion Loss in the NIR
- Resistant to Chemical, Physical, and Thermal Damage
- Suitable for High Power Applications
- Range of Standard Sizes and Custom Options Available

Coming Polarcor™ Glass Polarizers feature a high extinction ratio and low insertion loss at wavelengths in the NIR. These linear polarizers consist of elongated silver crystals aligned within a borosilicate glass substrate, providing a polarization mechanism based on resonant absorption. This polarization mechanism causes light of unwanted polarization directions to be absorbed, ensuring that stray light is eliminated. Coming Polarcor™ Glass Polarizers can be used to polarize light, block polarized light, reduce reflections, improve image contrast, modulate and control the intensity of light, or improve the signal to noise ratio. These polarizers are ideal for integration into polarization-dependent optical isolators, optical modulators, and other polarization-based devices in the telecommunications, medical, and defense industries.