

25mm FL SWIR Series Fixed Focal Length Lens



Stock #68-688 **1 In Stock**

[Similar Products](#)

⊖ 1 ⊕ £1,829⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£1,829.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
1" SWIR Series Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

Length (mm):

43.00

Maximum Diameter (mm):

43

Outer Diameter (mm):

43

Weight (g):

135

Optical Properties

Field of View @ Min Working Distance (mm):

150.00

Horizontal Field of View, 1" Sensor:

29.3°

Maximum Image Circle (mm):

16.00

Focal Length FL (mm):

25.00

Working Distance (mm):

300 - ∞

Aperture (f/#):

f/1.4 - f/16

Distortion (%):

<-1.0

Maximum Distortion (%):

-1

Lens Wavelength Range:

SWIR

Sensor

Maximum Sensor Format:

1"

Pixel Size (µm):

4.50

Threading & Mounting

Filter Thread:

M35.5 x 0.5

Mount:

C-Mount

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Contains SVHC\(s\)](#)

Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

Technical Information

SWIR Fixed Focal Length Lenses



