

**TECHSPEC®**

**25mm H x 50mm L x -75mm FL VIS-NIR Coated, Illumination Grade PCV Cylinder Lens**



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#69-848** **6 In Stock**

⊖ 1 ⊕ £119.<sup>00</sup>

**ADD TO CART**

Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-5    | £119.00 each                  |
| Qty 6-25   | £107.00 each                  |
| Qty 26-49  | £103.00 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cylinder Lens, Plano-Concave **Type:**

**Physical & Mechanical Properties**

4.00 **Center Thickness CT (mm):**

|  |  |
|--|--|
| ±0.1   | <b>Center Thickness Tolerance (mm):</b>                      |
| +0.0/-0.2  | <b>Dimensional Tolerance (mm):</b>                           |
| 25.0 x 50.0  | <b>Dimensions (mm):</b>                                      |
| 5.97   | <b>Edge Thickness ET (mm):</b>                               |
| <b>Optical Properties</b>  |  |
| -75.00   | <b>Effective Focal Length EFL (mm):</b>                      |
| <b>N-BK7</b>   | <b>Substrate:</b> <input type="checkbox"/>                   |
| VIS-NIR (400-1000nm)   | <b>Coating:</b>  |
| 400 - 1000   | <b>Wavelength Range (nm):</b>                                |
| -77.64   | <b>Back Focal Length BFL (mm):</b>                           |
| R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm | <b>Coating Specification:</b>                                |
| ±3   | <b>Focal Length Tolerance (%):</b>                           |
| -38.76   | <b>Radius R<sub>1</sub> (mm):</b>                            |
| 60-40  | <b>Surface Quality:</b>                                      |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns  | <b>Damage Threshold, By Design:</b> <input type="checkbox"/> |

|                              |                                    |
|------------------------------|------------------------------------|
| <b>Regulatory Compliance</b> |                                    |
| <b>Compliant</b>             | <b>RoHS 2015:</b>                  |
| <b>View</b>                  | <b>Certificate of Conformance:</b> |
| <b>Compliant</b>             | <b>Reach 235:</b>                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
- Circular and Rectangular Form Factors
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.

The thin lens approximation for the length of a line generated by a negative cylinder lens is:  $L = 2 * (r_0/f) * (z + f)$  where L is the line length,  $r_0$  is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

## Technical Information



## Coating Curves

---