

## TECHSPEC® 25mm, f/5.6 Sealed UCw Series Fixed Focal Length Lens



UCw Series Fixed Focal Length Lenses

Stock #70-619 **2 In Stock**

⊖ 1 ⊕ £225<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£225.60 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Ucw Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens with Compact Form Factor **Imaging Lens Type:**

#### Physical & Mechanical Properties

**Iris Option:**

Fixed

28.17 Length (mm):

38 Maximum Diameter (mm):

38 Outer Diameter (mm):

3.44 Maximum Rear Protrusion (mm):

31.28 Maximum Length (mm):

## Optical Properties

16.4° Horizontal Field of View @ Max Sensor Format:

16.4° Horizontal Field of View, 1/1.8" Sensor:

14.6° Horizontal Field of View, 1/2" Sensor:

13.2° Horizontal Field of View, 1/2.5" Sensor:

11.0° Horizontal Field of View, 1/3" Sensor:

8.2° Horizontal Field of View, 1/4" Sensor:

9.00 Maximum Image Circle (mm):

0.01 Numerical Aperture NA, Object Side:

7 (5) Number of Elements (Groups):

25.00 Focal Length FL (mm):

200 - ∞ Working Distance (mm):

f/5.6 Aperture (f#):

M4 MgF<sub>2</sub> Coating:

M4 MgF<sub>2</sub> Coating Specification:

15.05 Entrance Pupil Position (mm):

29.11 Object Space Principal Plane (mm):

-12.34 Image Space Principal Plane (mm):

-0.15 Maximum Distortion (%):

-44.48 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

## Sensor

1/2.5" Optimized Sensor Format:

1/1.8" Maximum Sensor Format:

1.85 Pixel Size (μm):

## Threading & Mounting

M25.5 x 0.50 (Female) Filter Thread:

C-Mount Mount:

## Environmental & Durability Factors

IPX7 Environmental Rating:

-20 to +60 For questions regarding operating temperature please contact our support team Storage Temperature (°C):

---

Waterproof (IPX7)

Type of Ruggedization:

---

## Regulatory Compliance

[View](#)

Certificate of Conformance:

---

## Product Details

- Up to 1/2", C-Mount Lens
- Ultra-Compact (UC), High Resolution Lens for Small Sensors
- Waterproof Versions of UC Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7

TECHSPEC® UCw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® UC Series Fixed Focal Length Lenses](#), and are designed to meet IEC Ingress Protection Codes IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes. Additionally, their compact size provides high performance at an affordable cost without sacrificing quality or feel. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface and are sealed with multiple O-rings to prevent moisture from entering the housing. TECHSPEC® UCw Series Fixed Focal Length Lenses are ideal for applications in space constrained, harsh environments such as food inspection, security, medical, and factory automation.

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.

**UCr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.

---