

[See all 49 Products in Family](#)

TECHSPEC®

2X, 300mm WD, In-Line CompactTL™ Telecentric Lens



300mm WD, 2X, In-Line Version (Left) and MS Version (Right)



Stock #33-115 13 In Stock

-

1

+

£936^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£936.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

CompactTL™ Series

Series:

Edmund Optics®

Manufacturer:

Telecentric Lens

Type:


In-Line Illumination		Type of Illumination:
Physical & Mechanical Properties		
Fixed	Iris Option:	
198.90	Length (mm):	
198.90	Length excluding Threads (mm):	
31	Maximum Diameter (mm):	
129	Weight (g):	
Optical Properties		
4.4mm	Horizontal Field of View, 2/3" Sensor:	
3.2mm	Horizontal Field of View, 1/2" Sensor:	
2.4mm	Horizontal Field of View, 1/3" Sensor:	
11.00	Maximum Image Circle (mm):	
0.035	Numerical Aperture NA, Object Side:	
±2	Working Distance Tolerance (mm):	
6 (5)	Number of Elements (Groups):	
0.049	Typical Telecentricity @ 588nm (°):	
0.0301	Typical Distortion @ 588nm (%):	
2X	Primary Magnification PMAG:	
2.00	Telecentric Lens Magnification:	
300	Working Distance (mm):	
4.4 x 3.3	FOV @ Max Sensor Format, H x V (mm):	
f/28.5	Aperture (f/#):	
λ/4 MgF ₂	Coating:	
±0.3mm (20% @ 20 lp/mm)	Depth of Field (mm):	
2X	Magnification:	
VIS	Lens Wavelength Range:	
Sensor		
2/3"	Maximum Sensor Format:	
4.50	Pixel Size (μm):	
Threading & Mounting		
M29.0 x 0.50 (Female)	Filter Thread:	
C-Mount	Mount:	
Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	REACH 241:	

Product Details


- 2/3", C-Mbunt Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


Technical Information




#33-115, 2X, 300mm WD, In-Line CompactTL™ Telecentric Lens, Distortion Plot




#33-115, 2X, 300mm WD, In-Line CompactTL™ Telecentric Lens, Relative Illumination Plot



#33-115, 2X, 300mm WD, In-Line CompactTL™ Telecentric Lens, Telecentricity Plot



#33-115, 2X, 300mm WD, In-Line CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f28.5



#33-115, 2X, 300mm WD, In-Line CompactTL™ Telecentric Lens, Depth of Field Plot, 300mm Working Distance, f28.5

