

**TECHSPEC® 3.0mm Diameter, N-BK7 Half-Ball Lens**



TECHSPEC® N-BK7 Half-Ball Lenses

Stock **#47-269** **20+ In Stock**

⊖ 1 ⊕ £43<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	£43.20 each
Qty 11-49	£38.80 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Half-Ball Lens **Type:**

**Physical & Mechanical Properties**

3.00 **Diameter (mm):**

±0.05 **Center Thickness Tolerance (mm):**

Radius R (mm):

1.50

Radius Tolerance ( $\mu\text{m}$ ):

+0.0/-1.5

Thickness (mm):

1.50

Diameter Tolerance ( $\mu\text{m}$ ):

$\pm 2.5$

## Optical Properties

Substrate:

N-BK7

Coating:

Uncoated

Wavelength Range (nm):

350 - 2200

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:

[View](#)

## Product Details

- Fiber Coupling Half-Spheres
- Collimating Lenses

TECHSPEC® N-BK7 Half-Ball Lenses are ideal for applications such as fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems. Half-ball (hemispherical) lenses can be interchanged with full ball lenses if the physical constraints of an application require a more compact design. These collimating lenses are uncoated, with a wavelength range of 350-2200nm. TECHSPEC® N-BK7 Half-Ball Lenses are offered in diameters ranging from 0.50 to 10.00mm.

## Technical Information

