

300µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-740 **NEW** 1 In Stock

- 1 +

£148^{.00}

ADD TO CART

Volume Pricing	
Qty	£148.00
1+	each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Physical & Mechanical Properties

Outer Diameter (mm):	25.4	Fixed Aperture Diameter (µm):	300 ± 5.0
Thickness (inches):	0.06 ±0.004	Thickness (mm):	1.52
Thickness Tolerance (mm):	±0.1		

Optical Properties

Coating:	Low Reflective Chrome
-----------------	-----------------------

Regulatory Compliance

Certificate of Conformance:	View
------------------------------------	----------------------

Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10µm to 1,000µm

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10µm to 1000µm. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.