

[See all 67 Products in Family](#)

## 35.5mm ID, 29.9mm Inner Length, IP67 C-Mount Lens Tube

See More by [LUCID Vision Labs™](#)



35.5mm ID IP67 C-Mount Lens Tube



Stock #13-739 **4 In Stock**

1 **£178<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>£178.40</b> each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Camera Accessory

Type:

IPTC-D355L299

Model Number:

29.9

Inner Length (mm):

**Note:**  
Compatible with Lucid Vision Labs Triton™ camera models

## Physical & Mechanical Properties

40.5      **Length (mm):**

41.0      **Outer Diameter (mm):**

35.5      **Inner Diameter (mm):**

## Sensor

Global      **Shutter Type:**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

## Product Details

- Compact 29 x 29 x 45mm Form Factor
- Global, Rolling, or Polarized CMOS Sensors
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x 29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.