

[See all 8 Products in Family](#)

38.1mm Dia. x 63.5mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) PCX Lens | CF-PX-38-63

See More by [ISP Optics](#)



Stock #24-805 CLEARANCE **1 In Stock**

− 1 + £208⁸⁰

ADD TO CART

Volume Pricing

Qty 1+	£208.80 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

CF-PX-38-63 **Model Number:**

Physical & Mechanical Properties

Diameter (mm):

38.10 +0.00/-0.13

<3 **Centering (arcmin):**

10.70 ±0.20 **Center Thickness CT (mm):**

10.70 **Edge Thickness ET (mm):**

34.29 **Clear Aperture CA (mm):**

Protective as needed **Bevel:**

Optical Properties

63.50 @ 5µm **Effective Focal Length EFL (mm):**

Uncoated **Coating:**

[Calcium Fluoride \(CaF₂\)](#) **Substrate:**

60-40 **Surface Quality:**

λ **Irregularity (P-V) @ 632.8nm:**

±2 **Focal Length Tolerance (%):**

25.10 **Radius R₁ (mm):**

1.67 **f#:**

0.30 **Numerical Aperture NA:**

300 - 8000 **Wavelength Range (nm):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Product Details

- Greater than 90% Transmission from 0.35-7µm
- Low Index of Refraction
- Ideal for Integration into Infrared Systems

ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses provide greater than 90% transmission from 350nm to 7µm and feature a low refractive index, allowing them to be used without an Anti-Reflection (AR) coating. Calcium Fluoride features a high laser damage threshold and low stress birefringence, making them highly suitable for integration into infrared systems. Additionally, calcium fluoride features low solubility and offers superior hardness to comparable fluoride-based substrates, making these PCX lenses capable of withstanding harsh environments and exposure to the elements. ISP Optics Calcium Fluoride Plano-Convex (PCX) Lenses are ideal for demanding applications that require superior performance from the visible through the mid-wave infrared (MMR) spectra.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools