

# 3.9mm CA, A-39N0-P16 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series - 6 pins FPC with Thermistor



3.9mm CA, A-39N0-P16 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series - 6 pins FPC with Thermistor



Stock **#15-740** CLEARANCE ☐ In Stock

1  **£96.01**

ADD TO CART

Qty 1+

£96.01

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
15.50

Coating:  
VS

|                                                                                                                                                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Packaged Lens w/ Thermistor                                                                                                         |
| <b>Clear Aperture CA (mm):</b><br>3.9                                                                                                               |
| <b>Contents of Kit:</b><br>Packaged A-39N0 with a straight flex cable with thermistor FPC-A-16 (6 pins)                                             |
| <b>Focus Range:</b><br>-5 to +15 diopter                                                                                                            |
| <b>Model Number:</b><br>A-39N0-P16                                                                                                                  |
| <b>Operating Temperature (°C):</b><br>-20 to +60                                                                                                    |
| <b>Storage Temperature (°C):</b><br>-40 to +85                                                                                                      |
| <b>Thickness (mm):</b><br>5.20                                                                                                                      |
| <b>Transmission (%):</b><br>97 @ 587nm                                                                                                              |
| <b>Transmitted Wavefront Error, RMS:</b><br>50nm                                                                                                    |
| <b>Typical Applications:</b><br>Industrial vision, medical imaging cameras, optical equipment, & biometric devices requiring a large clear aperture |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---