

TECHSPEC[®] 400, 800nm, 25.4mm Dia., Ultrafast Dual Band Mirror



Stock #24-322 13 In Stock

-

1

+

£177^{.55} £295.92

ADD TO CART

Volume Pricing	
Qty 1-5	£295.92 £177.55 each
Qty 6-9	£260.90 £156.54 each
Qty 10+	£233.76 £140.26 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Laser Mirror

Typical Applications:
Beam transport of 1st and 2nd harmonic of
Ti:Sapphire lasers

Physical & Mechanical Properties	
25.40 +0/-0.1	Diameter (mm):
6.35 ±0.10	Thickness (mm):
<3	Parallelism (arcmin):
>88	Clear Aperture (%):
Commercial Polish	Back Surface:
Optical Properties	
45	Angle of Incidence (°):
IBS (385-415, 770-830nm)	Coating:
400, 800	Design Wavelength DWL (nm):
Fused Silica (Corning 7980)	Substrate: ☐
10-5	Surface Quality:
R _s >99.9% @385-415nm R _p >99.8% @395-415nm R _s >99.9% @770-830nm R _p >99.9% @770-820nm	Coating Specification:
385 - 415, 770 - 830	Wavelength Range (nm):
λ/6	Surface Flatness (P-V):
S1: Dielectric S2: Stress-compensating	Coating Type:
<35fs ² @ 385 - 415nm (s-pol) <50fs ² @ 395 - 415nm (p-pol) <20fs ² @ 770 - 830nm (s-pol) <40fs ² @ 770 - 810nm (p-pol)	GDD Specification:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- High Reflectivity & Low Group Delay Dispersion (GDD) for Ultrafast Beam Steering
- Ion-Beam Sputtered (IBS) Coatings Minimize Scatter and Absorption Losses
- Near-Zero GDD for Both the First and Second Harmonics of Ti:sapphire and Yb-doped Lasers

TECHSPEC® Dual Band Low GDD Ultrafast Mirrors maintain high reflectivity and near-zero group delay dispersion over both the first and second harmonic of Ti:sapphire and Yb-doped lasers. Utilizing Ion-Beam Sputtered Coating Technology, these mirrors minimize scatter and absorption loss commonly observed when using other traditional coating application processes. TECHSPEC® Dual Band Low GDD Ultrafast Mirrors are often used in beam steering applications as they will maintain ultrashort pulse durations that can be difficult to preserve when using more conventional laser mirrors. These mirrors are ideal for second-harmonic generation (SHG) microscopy and spectroscopy applications as well as for frequency resolved optical gating (FROG).