

[See all 6 Products in Family](#)

TECHSPEC® 400, 800nm, 50.8mm Dia., Ultrafast Dual Band Mirror



Stock #24-323 **9 In Stock**

⊖ 1 ⊕ £576⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£576.00 each
Qty 6-9	£508.00 each
Qty 10+	£456.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror **Type:**

Typical Applications:
 Beam transport of 1st and 2nd harmonic of
 Ti:Sapphire lasers

Physical & Mechanical Properties

Thickness (mm):

9.53 ±0.10

50.80 +0/-0.1

Diameter (mm):

>88

Clear Aperture (%):

Commercial Polish

Back Surface:

<3

Parallelism (arcmin):

Optical Properties

Fused Silica (JGS1)

Substrate:

10-5

Surface Quality:

45

Angle of Incidence (°):

IBS (385-415, 770-830nm)

Coating:

400, 800

Design Wavelength DWL (nm):

385 - 415, 770 - 830

Wavelength Range (nm):

λ/6

Surface Flatness (P-V):

R_s>99.9% @385-415nm
R_p>99.8% @395-415nm
R_s>99.9% @770-830nm
R_p>99.9% @770-820nm

Coating Specification:

S1: Dielectric
S2: Stress-compensating

Coating Type:

<35fs² @ 385 - 415nm (s-pol)
<50fs² @ 395 - 415nm (p-pol)
<20fs² @ 770 - 830nm (s-pol)
<40fs² @ 770 - 810nm (p-pol)

GDD Specification:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- High Reflectivity & Low Group Delay Dispersion (GDD) for Ultrafast Beam Steering
- Ion-Beam Sputtered (IBS) Coatings Minimize Scatter and Absorption Losses
- Near-Zero GDD for Both the First and Second Harmonics of Ti:sapphire and Yb-doped Lasers

TECHSPEC® Dual Band Low GDD Ultrafast Mirrors maintain high reflectivity and near-zero group delay dispersion over both the first and second harmonic of Ti:sapphire and Yb-doped lasers. Utilizing Ion-Beam Sputtered Coating Technology, these mirrors minimize scatter and absorption loss commonly observed when using other traditional coating application processes. TECHSPEC® Dual Band Low GDD Ultrafast Mirrors are often used in beam steering applications as they will maintain ultrashort pulse durations that can be difficult to preserve when using more conventional laser mirrors. These mirrors are ideal for second-harmonic generation (SHG) microscopy and spectroscopy applications as well as for frequency resolved optical gating (FROG).