

405nm High Performance Laser Line Filter 12.5mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-268** **1 In Stock**

[Additional Bandwidths](#)

-

1

+

£322¹⁸

ADD TO CART

Volume Pricing	
Qty 1+	£322.18 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Bandpass Filter

Physical & Mechanical Properties

12.50 +0.0/-0.1	Diameter (mm):
≥10	Clear Aperture CA (mm):
±0.10	Thickness Tolerance (mm):
Mounted in Black Anodized Ring	Construction:

ML-C-48497AParagraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	Physical Durability:
2.0 ±0.1	Substrate Thickness (mm):

Optical Properties

0 ±2	Angle of Incidence (°):
1.5	Bandwidth (nm):

353.5 - 401 & 409.1 - 495.3	OD 5 Blocking Wavelength Range (nm) :
372.6 - 398.9 & 411.1 - 445.5	OD 6 Blocking Wavelength Range (nm):

≥6.0	Optical Density OD (Average):
405.00	Center Wavelength CWL (nm):

405	Design Wavelength DWL (nm):
1.50 - 2.8	Full Width-Half Max FWHM (nm):

Fused Silica	Substrate:
>90	Minimum Transmission (%):

Hard Coated	Coating:
60-40	Surface Quality:

>90	Transmission (%):
353.5 - 401 & 409.1 - 495.3	Blocking Wavelength Range (nm):

Threading & Mounting

3.5 ±0.1	Mount Thickness (mm):
----------	-----------------------

Environmental & Durability Factors

ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	Environmental Durability:
--	---------------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 209:

View	Certificate of Conformance:
------	-----------------------------







PRODUCT DETAILS

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisyspontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

TECHNICAL INFORMATION



COMPATIBLE MOUNTS
