

[See all 6 Products in Family](#)

**TECHSPEC® 405nm Laser Line Coated, Unmounted Anamorphic Prism Pair**



#65-933 405nm Laser Line Coated, Unmounted Anamorphic Prism Pair

Stock **#65-933** **8 In Stock**

⊖ 1 ⊕ £186<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£186.40 each
Qty 6-25	£168.00 each
Qty 26-49	£149.60 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Beam Shaping **Type:**

**Physical & Mechanical Properties**

+0.00/-0.10 **Dimensional Tolerance (mm):**

## Optical Properties

Coating:  
Laser V-Coat (405nm)

Design Wavelength DWL (nm):  
405

Substrate:   
N-SF11

Magnification:  
2X-6X (Depends on Mounting Configuration)

Surface Quality:  
20-10

Angle Tolerance (arcmin):  
3

Coating Specification:  
 $R_{\text{abs}} < 0.25\% @ 405\text{nm}$   
 $R_{\text{avg}} < 1.5\% @ 375 - 435\text{nm}$

Power (fringes) @ 632.8nm:  
3.00

Irregularity (fringes) @ 632.8nm:  
1.00

## Threading & Mounting

Mount:  
Unmounted

## Regulatory Compliance


Certificate of Conformance:  
[View](#)

## Product Details


- Converts Elliptical Beam to Circular
- Anti-Reflection Coated for Common Diode Wavelengths
- Mounted and Unmounted Versions Available

An anamorphic prism pair is used to expand a laser beam in one dimension. This makes it ideal for converting the elliptical beam shape of laser diodes into a nearly circular one. Mounting our unmounted anamorphic prism pair in the proper orientation will provide magnification ratios from 2:1 - 6:1. Designed at 650nm and broadband anti-reflection (BBAR) coated for 600 – 1050nm, it provides excellent performance at both 635nm and 670nm.

The center of the output beam is displaced 5.9mm from center of the input beam in our mounted anamorphic prism pair. The Dovetail Accessory Mount allows it to rotate with respect to the laser, simplifying bench-top mounting. The C-Accessory Mount allows our full line of [C-Mount components](#) to be used in conjunction with the mounted anamorphic prism pair.




## Technical Information




Ray path for anamorphic prism pairs, showing transformation of elliptical beam to circular beam

Typical Values				
Magnification	$\alpha 1$	$\alpha 2$	Vertical Separation (V)	Beam Displacement (D)
2X	-20.6°	-6.5°	1.75mm	4.50mm
3X	-29.7°	-0.9°	2.56mm	5.45mm
4X	-34.1°	2.1°	3.01mm	5.74mm
5X	-37.4°	3.2°	3.33mm	6.15mm
6X	-39.7°	4.0°	3.51mm	6.42mm

**Anamorphic Prism Pair**



**Magnification vs. Prism Angles**



**Beam Expander Mounting Configurations.**

Click on an item below to be brought to that item's product page.

