

[See all 52 Products in Family](#)

TECHSPEC® 500nm 50mm Diameter, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#64-699** **20+ In Stock**

⊖ 1 ⊕ £192⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£192.00 each
Qty 6-25	£163.20 each
Qty 26-49	£153.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Longpass Filter **Type:**

Physical & Mechanical Properties

50.00 +0.00/-0.20 **Diameter (mm):**

Thickness (mm):

5.00 ±0.1

Clear Aperture (%):

80

Optical Properties

Angle of Incidence (°):

0

Optical Density OD (Average):

≥2.0

Cut-On Wavelength (nm):

500.00

Substrate:

Fused Silica (Corning 7980)

Coating:

Traditional Coated

Rejection Wavelength (nm):

200 - 480

Surface Quality:

40-20

Transmission (%):

>85

Transmission Wavelength (nm):

520 - 2000

Transmitted Wavefront, P-V:

λ/4

Cut-On Tolerance (%):

±2

Slope Factor (%):

3.00

Coating Specification:

Surface 1: Multi-Layer Dielectric
Surface 2: MgF₂

Wavelength Range (nm):

200 - 2000

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Sharp Cut-On Wavelength
- High Rejection/Transmission Efficiency
- Precision Fused Silica Substrate
- Variety of [OD 2.0 Longpass Filter Kits](#) are Available

TECHSPEC® OD 2.0 Longpass Filters are designed to have a sharp transition from reflection to transmission, making them ideal for various applications. Available in a variety of cut-on wavelengths, these filters are designed for fluorescence and order sorting applications. These filters feature precision fused silica substrate and high rejection/transmission efficiency. TECHSPEC® OD 2.0 Longpass Filters have a single-layer AR coating on the back surface that enhances the overall efficiency of each filter. Eliminate stray light by creating custom bandpass filters when combined with [TECHSPEC® OD 2.0 Shortpass Filters](#). A single layer AR coating on the back surface enhances the overall efficiency of each filter.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Technical Information



Compatible Mounts