

[See all 14 Products in Family](#)

50.8 x 500mm, Gimbal Crossmember Plate, English

See More by [Zaber™](#)



500mm, Gimbal Crossmember Plate

Stock **#71-115** **1 In Stock**

⊖ 1 ⊕ £228⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£228.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounting Plate **Type:**
Zaber Technologies Inc. **Manufacturer:**

Physical & Mechanical Properties

50.80 **Length (mm):**

9.50	Thickness (mm):
500.00	Width (mm):
1.12	Weight (kg):

Threading & Mounting

(17) 1/4-20 tapped (8) M4 x0.7	Mounting Threads:
-----------------------------------	--------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- 360° Continuous Travel
- Speed up to 24°/s, Max Torque of 10N-m
- Max Centered Payload of 15kg; Max Cantilevered Load Capacity of 20N-m
- 300 and 500mm Payload Width Frame Options Available

Zaber™ High Load Capacity Motorized Gimbals are large, motorized two-axis rotation platforms that simplify the angular positioning of large components or subsystems within an optical system. All gimbals feature 360° continuous travel, two axis rotation around a single point, speed up to 24°/s, a Cantilevered Load Capacity of 20N-m, a rotary quadrature encoder resolution of 200 counts per revolution (CPR), and are available for payload widths of either 300 or 500mm. Drilled and tapped crossmember plates, used to create a mounting platform within the gimbal, are available with either English ([#71-113](#) or [#71-115](#)) or Metric ([#71-112](#) or [#71-114](#)) mounting options, and can also be used to quickly swap different components or pre-built subsystems into the gimbal. Zaber™ High Load Capacity Motorized Gimbals feature built-in controllers and motors allowing for closed-loop operation, slip/stall recovery, and independent axis control via a single RS-232 or USB connection for plug-and-play functionality and easy system integration. These gimbals are ideal for telecom, scanning, and tracking applications where high-load capacity and high-precision angular positioning is required.

Note: A [48 VDC universal power supply](#), [data cables](#) for daisy chaining, and computer interface cables ([USB](#) or [RS-232](#)) are sold separately as accessories. All Zaber™ High Load Capacity Motorized Gimbals are compatible with [Zaber Launcher](#) and [Zaber's Motion Library](#).